

Varistar CP Double Steel Door, Plain, 3-Point Locking



Perforated Varistar CP steel double door with 3-point locking for applications with IP 20 protection.

FEATURES

Double steel door with 3 point locking for IP 20 protection class

Lever handle with key insert (2 keys)

Opening angle 180°

Standard fitting, lock on right-hand door

Can be retrofitted with lever handle 24630003 and DIN profile half cylinder with keys or push button

SPECIFICATIONS

Locking Type: 3-Point Locking

Product Type: Cabinet Door

Protection Rating: IP20

Material: Steel

Table 1/2

Catalog Number	Rack Height	Height	Width	Package Quantity	Color	Color Code
21630-440	24U	1200mm	600mm	1	Black Grey	RAL 7021
21630-441	24U	1200mm	800mm	1	Black Grey	RAL 7021
21630-442	29U	1400mm	600mm	1	Black Grey	RAL 7021

CatalogNumber	Rack Height	Height	Width	Package Quantity	Color	Color Code
21630-443	29U	1400mm	800mm	1	Black Grey	RAL 7021
21630-444	33U	1600mm	600mm	1	Black Grey	RAL 7021
21630-445	33U	1600mm	800mm	1	Black Grey	RAL 7021
21630-446	38U	1800mm	600mm	1	Black Grey	RAL 7021
21630-447	38U	1800mm	800mm	1	Black Grey	RAL 7021
21630-086	42U	2000mm	600mm	1	Black Grey	RAL 7021
21630-089	42U	2000mm	800mm	1	Black Grey	RAL 7021
21630-087	47U	2200mm	600mm	1	Black Grey	RAL 7021
21630-090	47U	2200mm	800mm	1	Black Grey	RAL 7021
21630-088	52U	2450mm	600mm	1	Black Grey	RAL 7021
21630-091	52U	2450mm	800mm	1	Black Grey	RAL 7021

Table 2/2

Catalog Number	Complies With	Finish	Type	Works With	Quick Ship
21630-440	IEC 61587-1, IEC 61587-3	Powder Coated	Steel Double Door	Varistar CP	No
21630-441	IEC 61587-1, IEC 61587-3	Powder Coated	Steel Double Door	Varistar CP	No
21630-442	IEC 61587-1, IEC 61587-3	Powder Coated	Steel Double Door	Varistar CP	No
21630-443	IEC 61587-1, IEC 61587-3	Powder Coated	Steel Double Door	Varistar CP	No
21630-444	IEC 61587-1, IEC 61587-3	Powder Coated	Steel Double Door	Varistar CP	No
21630-445	IEC 61587-1, IEC 61587-3	Powder Coated	Steel Double Door	Varistar CP	No

Catalog Number	Complies With	Finish	Type	Works With	Quick Ship
21630-446	IEC 61587-1, IEC 61587-3	Powder Coated	Steel Double Door	Varistar CP	No
21630-447	IEC 61587-1, IEC 61587-3	Powder Coated	Steel Double Door	Varistar CP	No
21630-086	IEC 61587-1, IEC 61587-3	Powder Coated	Steel Double Door	Varistar CP	No
21630-089	IEC 61587-1, IEC 61587-3	Powder Coated	Steel Double Door	Varistar CP	No
21630-087	IEC 61587-1, IEC 61587-3	Powder Coated	Steel Double Door	Varistar CP	No
21630-090	IEC 61587-1, IEC 61587-3	Powder Coated	Steel Double Door	Varistar CP	No
21630-088	IEC 61587-1, IEC 61587-3	Powder Coated	Steel Double Door	Varistar CP	No
21630-091	IEC 61587-1, IEC 61587-3	Powder Coated	Steel Double Door	Varistar CP	No

ADDITIONAL PRODUCT DETAILS

24U - 33U IP20 doors have 2 hinges, 38U - 52U IP20 doors have 3 hinges to ensure robust IP20 closing structures for taller cabinets

Please order lever handle 24630003 and the DIN lock separately if you want to replace the 1333 DIN lock lever handle

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE