

Plain Doors For Floor Standing Enclosures, DN-NC



This door replaces the rear panel in a floor standing enclosure to allow for rear access of equipment installed in the front, or for using back to back mounting plates to increase the enclosure's mounting space.

FEATURES

Finish: RAL 7035 structured powder coating.

Mounting requirements: Use hinge kit DNMK-NC if no door was fitted previously.

Maximum load: 800 N.

Pack quantity: 1 piece.

Description: Standard door equipped with double-bit 3 mm lock system and door frame. Door accessory kit DNMK (hinges, rod catches) to be ordered separately. Allows all the options of the locking program and 180° hinges. Compatible with combinable and compact enclosure ranges.

Material: 2 mm steel plate.

SPECIFICATIONS

Table 1/1

Catalog Number	Height	Width	Enclosure Material	Product Family	Material	Finish
DNNCDHT1805L R5	1800mm	1000mm	Mild Steel	Free-Standing	Mild Steel	Powder Coated
DNNCDHT1805R R5	1800mm	1000mm	Mild Steel	Free-Standing	Mild Steel	Powder Coated
DNNCDHT1806L R5	1800mm	1200mm	Mild Steel	Free-Standing	Mild Steel	Powder Coated
DNNCDHT1806R R5	1800mm	1200mm	Mild Steel	Free-Standing	Mild Steel	Powder Coated
DNNCDHT2005L R5	2000mm	1000mm	Mild Steel	Free-Standing	Mild Steel	Powder Coated
DNNCDHT2005R R5	2000mm	1000mm	Mild Steel	Free-Standing	Mild Steel	Powder Coated
DNNCDHT2006L R5	2000mm	1200mm	Mild Steel	Free-Standing	Mild Steel	Powder Coated
DNNCDHT2006R R5	2000mm	1200mm	Mild Steel	Free-Standing	Mild Steel	Powder Coated
DNNCDHT2206L R5	2200mm	1200mm	Mild Steel	Free-Standing	Mild Steel	Powder Coated
DNNCDHT2206R R5	2200mm	1200mm	Mild Steel	Free-Standing	Mild Steel	Powder Coated
DNNCSHT1806R 5	1800mm	600mm	Mild Steel	Free-Standing	Mild Steel	Powder Coated
DNNCSHT1808R 5	1800mm	800mm	Mild Steel	Free-Standing	Mild Steel	Powder Coated
DNNCSHT2006R 5	2000mm	600mm	Mild Steel	Free-Standing	Mild Steel	Powder Coated

Catalog Number	Height	Width	EnclosureMaterial	Product Family	Material	Finish
DNNCSHT2008R5	2000mm	800mm	Mild Steel	Free-Standing	Mild Steel	Powder Coated
DNNCSHT2208R5	2200mm	800mm	Mild Steel	Free-Standing	Mild Steel	Powder Coated
DNNCDHT1606LR5	1600mm	600mm	Mild Steel	Free-Standing	Mild Steel	Powder Coated
DNNCDHT1606RR5	1600mm	600mm	Mild Steel	Free-Standing	Mild Steel	Powder Coated
DNNCSHT1606R5	1600mm	600mm	Mild Steel	Free-Standing	Mild Steel	Powder Coated
DNNCSHT1608R5	1600mm	800mm	Mild Steel	Free-Standing	Mild Steel	Powder Coated
DNNCSHT1810R5	1800mm	1000mm	Mild Steel	Free-Standing	Mild Steel	Powder Coated
DNNCSHT2010R5	2000mm	1000mm	Mild Steel	Free-Standing	Mild Steel	Powder Coated
DNNCSHT2206R5	2200mm	600mm	Mild Steel	Free-Standing	Mild Steel	Powder Coated

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE