

# Snap in cable management finger kit

## CATALOG NUMBER

**24630-057**



The hand mountable cable fingers ensure an optimal cable radius and prevent damage or breakage by ensuring an appropriate cable bend radius. The flexible T shaped structures protect the cables so that the structured cabling system remains undamaged and fully functional.

## FEATURES

T-shaped cable fingers installable directly on the 19" panel mounts without screws allow for easy and clean management of copper and fiber optic cables, etc.

Each 5-Finger unit can be individually snapped on to the 19" upright based on the cable management requirements

The cable fingers protrude 81,5mm from the 19" upright, hence needs a minimum recess of ~82mm

Finger spacing of 36,45mm for high density cabling

Works only with Datacom 19" uprights / panel mounts with printed U Height identification - 24630013, 24630014 and 24630015

## PRODUCT ATTRIBUTES

Product Type: Cable Support

Product Family: Varistar CP

Type: Finger Kit

Material: PVC

Color: Black

Package Quantity: 20

Net Weight: 1.98kg

## ADDITIONAL PRODUCT DETAILS

Easy snap in kit for cable management, allows customers to build the cable finger duct using smaller units

**WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

**Europe**

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

**Asia**

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

**Middle East & India**

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**