


Varistar CP Top Cover Fan



Varistar Fan Top Cover with 3 Fans, expandable to 6 fans.

FEATURES

3 axial fans fitted (maximum: 6 fans)

C14 Socket

SPECIFICATIONS

Product Type: Fan **Material:** Steel

Table 1/2						
Catalog Number	Width	Depth	Package Quantity	Color	Color Code	Finish
21630-597	600mm	600mm	1	Black Grey	RAL 7021	Powder Coated
21630-598	600mm	800mm	1	Black Grey	RAL 7021	Powder Coated
21630-736	800mm	600mm	1	Black Grey	RAL 7021	Powder Coated
21630-737	800mm	800mm	1	Black Grey	RAL 7021	Powder Coated
21630-738	800mm	900mm	1	Black Grey	RAL 7021	Powder Coated
21630-739	800mm	1000mm	1	Black Grey	RAL 7021	Powder Coated
21630-599	600mm	900mm	1	Black Grey	RAL 7021	Powder Coated
21630-600	600mm	1000mm	1	Black Grey	RAL 7021	Powder Coated
21630-601	600mm	1100mm	1	Black Grey	RAL 7021	Powder Coated
21630-602	600mm	1200mm	1	Black Grey	RAL 7021	Powder Coated
21630-603	600mm	600mm	1	Black Grey	RAL 7021	Powder Coated
21630-604	600mm	800mm	1	Black Grey	RAL 7021	Powder Coated
21630-605	600mm	900mm	1	Black Grey	RAL 7021	Powder Coated
21630-606	600mm	1000mm	1	Black Grey	RAL 7021	Powder Coated
21630-607	600mm	1100mm	1	Black Grey	RAL 7021	Powder Coated
21630-608	600mm	1200mm	1	Black Grey	RAL 7021	Powder Coated
21630-609	800mm	600mm	1	Black Grey	RAL 7021	Powder Coated
21630-610	800mm	800mm	1	Black Grey	RAL 7021	Powder Coated

CatalogNumber	Width	Depth	Package Quantity	Color	Color Code	Finish
21630-611	800mm	900mm	1	Black Grey	RAL 7021	Powder Coated
21630-612	800mm	1000mm	1	Black Grey	RAL 7021	Powder Coated
21630-613	800mm	1100mm	1	Black Grey	RAL 7021	Powder Coated
21630-614	800mm	1200mm	1	Black Grey	RAL 7021	Powder Coated
21630-740	800mm	1100mm	1	Black Grey	RAL 7021	Powder Coated
21630-741	800mm	1200mm	1	Black Grey	RAL 7021	Powder Coated

Table 2/2						
Catalog Number	Protection Rating	Works With	Quick Ship			
21630-597	IP20		No			
21630-598	IP20		No			
21630-736	IP20		No			
21630-737	IP20		No			
21630-738	IP20		No			
21630-739	IP20		No			
21630-599	IP20		No			
21630-600	IP20		No			
21630-601	IP20		No			
21630-602	IP20		No			
21630-603		Varistar CP	No			

Catalog Number	Protection Rating	Works With	Quick Ship
21630-604		Varistar CP	No
21630-605		Varistar CP	No
21630-606		Varistar CP	No
21630-607		Varistar CP	No
21630-608		Varistar CP	No
21630-609		Varistar CP	No
21630-610		Varistar CP	No
21630-611		Varistar CP	No
21630-612		Varistar CP	No
21630-613		Varistar CP	No
21630-614		Varistar CP	No
21630-740	IP20		No
21630-741	IP20		No

ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit, power cable, Thermostat or Speed controller separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations +1.763.422.2661 Chat with us: nvent.com/schroff

Europe

Straubenhardt, Germany +49.7082.794.0 Betschdorf, France +33.3.88.90.64.90 Warsaw, Poland +48.22.209.98.35 Assago, Italy +39.02.932.7141 Chat with us: nvent.com/schroff

Asia

Shanghai, China +86.21.2412.6943 Qingdao, China +86.532.8771.6101 Singapore +65.6768.5800 Shin-Yokohama, Japan +81.45.476.0271 Chat with us: nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates +971.4.378.1700 Bangalore, India +91.80.6715.2001 Istanbul, Turkey +90.216.250.7374 Chat with us: nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE