

Air Terminal Base, Pipe Mount Bonding, Imperial Thread



CERTIFICATIONS





FEATURES

Mounts air terminal to horizontal pipe or vertical pipe using Right Angle Extension Adaptor


SPECIFICATIONS


Table 1/2							
Catalog Number	Material	Finish	Thread Size (TS)	Outer Diameter (OD)	Depth (D)	Width (W)	
LPA37258	Aluminum		5/8" UNC	38.1 - 63.5 mm	41.4mm	92 mm	
LPA37212	Aluminum		1/2" UNC	38.1 - 63.5 mm	41.4mm	92 mm	
LPC372L12	Copper	Tinned	1/2" UNC	38.1 - 63.5 mm	41.4mm	92 mm	
LPC372L38	Copper	Tinned	3/8" UNC	38.1 - 63.5 mm	41.4mm	92 mm	

CatalogNumber	Material	Finish	Thread Size (TS)	Outer Diameter (OD)	Depth (D)	Width (W)
LPC37258	Copper		5/8" UNC	38.1 - 63.5 mm	41.4mm	92 mm
LPC37238	Copper		3/8" UNC	38.1 - 63.5 mm	41.4mm	92 mm
LPC37212	Copper		1/2" UNC	38.1 - 63.5 mm	41.4mm	92 mm
LPC372L58	Copper	Tinned	5/8" UNC	38.1 - 63.5 mm	41.4mm	92 mm

Table 2/2							
Catalog Number	Unit Weight	Certifications					
LPA37258	0.15 kg	E202878-Combined_CoC, E202878-Combined_CoC					
LPA37212	0.15 kg	E202878-Combined_CoC, E202878-Combined_CoC					
LPC372L12	0.35 kg						
LPC372L38	0.35 kg						
LPC37258	0.35 kg						
LPC37238	0.35 kg						
LPC37212	0.35 kg						
LPC372L58	0.35 kg						

DIAGRAMS





WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

 $^{\Delta}$ WARNING: This product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

North America

+1.800.753.9221 Option 1 – Customer Care Option 2 - Technical Support

Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

APAC

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE