

Ventilation Roofs, CVR

The ventilation roof plate provides cost effective natural ventilation while keeping insects and dust out.



FEATURES

Description: Raised roof with 2.5 mm ventilation slots and filter material.

Material: 1.5 mm steel plate. Filter material: EU 4 according to DIN 24185.

Finish: RAL 7035 structured powder coating.

Temperature resistance: 100 °C.

Protection: Complies with IP 31, TYPE 1.

Pack quantity: 1 piece with mounting brackets and ventilation filter.

Note: Increases the enclosure height by 40 mm.

SPECIFICATIONS

Thickness:	1.5mm
Color:	Light Gray
Material:	Mild Steel
Finish:	Powder Coated
Color Code:	RAL 7035

Table 1/1

Catalog Number	Article Number	Height	Width	Depth	Product Family	Enclosure Material
CVR0505R5	CVR0505R5	58mm	500mm	500mm	Free-Standing	Mild Steel
CVR0603R5	CVR0603R5	58mm	600mm	300mm	Free-Standing	Mild Steel
CVR0604R5	CVR0604R5	58mm	600mm	400mm	Free-Standing	Mild Steel
CVR0605R5	CVR0605R5	58mm	600mm	500mm	Free-Standing	Mild Steel
CVR0606R5	CVR0606R5	58mm	600mm	600mm	Free-Standing	Mild Steel
CVR0608R5	CVR0608R5	58mm	600mm	800mm	Free-Standing	Mild Steel
CVR0803R5	CVR0803R5	58mm	800mm	300mm	Free-Standing	Mild Steel
CVR0804R5	CVR0804R5	58mm	800mm	400mm	Free-Standing	Mild Steel
CVR0805R5	CVR0805R5	58mm	800mm	500mm	Free-Standing	Mild Steel
CVR0806R5	CVR0806R5	58mm	800mm	600mm	Free-Standing	Mild Steel
CVR0808R5	CVR0808R5	58mm	800mm	800mm	Free-Standing	Mild Steel
CVR0809R5	CVR0809R5	58mm	800mm	900mm	Free-Standing	Mild Steel
CVR1003R5	CVR1003R5	58mm	1000mm	300mm	Free-Standing	Mild Steel
CVR1004R5	CVR1004R5	58mm	1000mm	400mm	Free-Standing	Mild Steel
CVR1005R5	CVR1005R5	58mm	1000mm	500mm	Free-Standing	Mild Steel
CVR1006R5	CVR1006R5	58mm	1000mm	600mm	Free-Standing	Mild Steel

Catalog Number	Article Number	Height	Width	Depth	Product Family	EnclosureMaterial
CVR1008R5	CVR1008R5	58mm	1000mm	800mm	Free-Standing	Mild Steel
CVR1203R5	CVR1203R5	58mm	1200mm	300mm	Free-Standing	Mild Steel
CVR1204R5	CVR1204R5	58mm	1200mm	400mm	Free-Standing	Mild Steel
CVR1205R5	CVR1205R5	58mm	1200mm	500mm	Free-Standing	Mild Steel
CVR1206R5	CVR1206R5	58mm	1200mm	600mm	Free-Standing	Mild Steel
CVR1208R5	CVR1208R5	58mm	1200mm	800mm	Free-Standing	Mild Steel
CVR1604R5	CVR1604R5	58mm	1600mm	400mm	Free-Standing	Mild Steel
CVR1605R5	CVR1605R5	58mm	1600mm	500mm	Free-Standing	Mild Steel
CVR1606R5	CVR1606R5	58mm	1600mm	600mm	Free-Standing	Mild Steel

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE