nVent CADDY

We connect and protect

# Flexible Plastic Conduit and Pipe Clamp

## FEATURES

- Push-in installation of conduit
- Flexible clamping design accommodates multiple conduit sizes using one clamp
- Compatible with different structural attachment components to accommodate a variety of structures including concrete, brick, plywood, cable tray, spring steel fasteners and threaded rod
- Snap-together clips can be easily assembled to limit the number of fixing points to structure
- Low profile allows for installations in tight spaces
- Non-flame propagating per IEC 61386-25
- Passed 650°C glowing/hot-wire wire test per EN 60695-2
- Suitable for insulated and non-insulated pipe applications
- Push-in installation of conduit
- Halogen free
- UV-stabilized
- Compliance to AS3500
- Withstands up to 40kg of extraction force

## SPECIFICATIONS

**Material:** Polypropylene

**Temperature:** -10 to 85 °C

Table 1/1

| Catalog Number | Article Number | Outer Diameter (OD) | A | B |
|---|---|---|---|---|

| | | | | |
|---|---|---|---|---|
| SCFC1620 | 800020 | 16 - 20 mm | 32 mm | 16 - 18 mm |
| SCFC2025 | 800021 | 20 - 25 mm | 32 mm | 18.0 - 20.5 mm |
| SCFC2532 | 800022 | 25 - 32 mm | 32 mm | 20.5 - 24 mm |
| SCFC3240 | 800023 | 32 - 40 mm | 32 mm | 24 - 28 mm |
| SCFC4050 | 800024 | 40 - 50 mm | 32 mm | 28 - 33 mm |

## DIAGRAMS




## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**
+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

**Europe**
Netherlands:
+31 800-0200135
France:
+33 800 901 793

**Europe**
Germany:
800 1890272
Other Countries:
+31 13 5835404

**APAC**
Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

Our powerful portfolio of brands:
CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.