

EuropacPRO 19" Subrack Kit for Backplane, Heavy, Retrofit Shielding

Power Utilities

Rear horizontal rail for backplane mounting with insulation strip



CERTIFICATIONS



FEATURES

Horizontal rail type "Heavy"

Shock and Vibration resistance up to 5 g

IP 20, in accordance with IEC 60529

Shock and vibration tested to the German "Bahn" standards BN 411002, BN 411003

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

Installed load up to 15 kg

Version without front handles

Supplied as space-saving flat-pack

SPECIFICATIONS

Table 1/3

Catalog Number	Rack Height	Depth	Package Quantity	For Mounting	Board Depth	Shock and Vibration Tolerance
24563-161	3 U	175 mm	1	Backplane	160 mm	5 g (force)
24563-162	3 U	235 mm	1	Backplane	160 mm, 220 mm	5 g (force)
24563-163	3 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	5 g (force)
24563-164	3 U	355 mm	1	Backplane	160 mm, 220 mm, 280 mm, 340 mm	5 g (force)
24563-461	6 U	175 mm	1	Backplane	160 mm	5 g (force)
24563-462	6 U	235 mm	1	Backplane	160 mm, 220 mm	5 g (force)
24563-463	6 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	5 g (force)
24563-464	6 U	355 mm	1	Backplane	160 mm, 220 mm, 280 mm, 340 mm	5 g (force)

Table 2/3

Catalog Number	Handle Included	Mounting	Complies With	EMC Shielding	Product Type	Rack Width
24563-161	No	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP
24563-162	No	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP
24563-163	No	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP
24563-164	No	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP
24563-461	No	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP
24563-462	No	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP
24563-463	No	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP

CatalogNumber	HandleIncluded	Mounting	Complies With	EMC Shielding	Product Type	Rack Width
24563-464	No	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP

Table 3/3

Catalog Number	Static Load
24563-161	15 kgf
24563-162	15 kgf
24563-163	15 kgf
24563-164	15 kgf
24563-461	15 kgf
24563-462	15 kgf
24563-463	15 kgf
24563-464	15 kgf

ADDITIONAL PRODUCT DETAILS

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE