

# VJ Mounting Plate

VJ Mounting Plates allow convenient component mounting inside VJ enclosures.



## FEATURES

---

Allows convenient component mounting inside VJ enclosures

## SPECIFICATIONS

| Table 1/1      |                |        |       |       |            |               |
|----------------|----------------|--------|-------|-------|------------|---------------|
| Catalog Number | Article Number | Height | Width | Depth | Material   | Finish        |
| MP1008A        | MP1008A        | 254mm  | 203mm | 2mm   | Aluminum   | Mill          |
| MP1210A        | MP1210A        | 305mm  | 254mm | 2mm   | Aluminum   | Mill          |
| MP1412A        | MP1412A        | 356mm  | 305mm | 2mm   | Aluminum   | Mill          |
| MP1614A        | MP1614A        | 406mm  | 356mm | 2mm   | Aluminum   | Mill          |
| MP1816A        | MP1816A        | 457mm  | 406mm | 2mm   | Aluminum   | Mill          |
| MP2016A        | MP2016A        | 508mm  | 406mm | 2mm   | Aluminum   | Mill          |
| MP606A         | MP606A         | 152mm  | 152mm | 2mm   | Aluminum   | Mill          |
| MP806A         | MP806A         | 203mm  | 152mm | 2mm   | Aluminum   | Mill          |
| MP3024A        | MP3024A        | 762mm  | 610mm | 2mm   | Aluminum   | Mill          |
| MP3030A        | MP3030A        | 762mm  | 762mm | 2mm   | Aluminium  |               |
| MP1008S        | MP1008S        | 254mm  | 203mm | 2.5mm | Mild Steel | Powder Coated |
| MP1210S        | MP1210S        | 305mm  | 254mm | 2.5mm | Mild Steel | Powder Coated |
| MP1412S        | MP1412S        | 356mm  | 305mm | 2.5mm | Mild Steel | Powder Coated |
| MP1614S        | MP1614S        | 406mm  | 356mm | 2.5mm | Mild Steel | Powder Coated |
| MP1816S        | MP1816S        | 457mm  | 406mm | 2.5mm | Mild Steel | Powder Coated |
| MP2016S        | MP2016S        | 508mm  | 406mm | 2.5mm | Mild Steel | Powder Coated |
| MP606S         | MP606S         | 152mm  | 152mm | 2.5mm | Mild Steel | Powder Coated |
| MP806S         | MP806S         | 203mm  | 152mm | 2.5mm | Mild Steel | Powder Coated |
| MP3024S        | MP3024S        | 762mm  | 610mm | 2.5mm | Mild Steel | Powder Coated |

| Catalog Number | Article Number | Height | Width | Depth | Material     | Finish       |
|----------------|----------------|--------|-------|-------|--------------|--------------|
| MP3030S        | MP3030S        | 762mm  | 762mm | 2.5mm | Mild Steel   | Power Coated |
| MP606N         | MP606N         | 152mm  | 152mm | 6.4mm | Non-Metallic | Smooth Matte |
| MP1008N        | MP1008N        | 254mm  | 203mm | 6.4mm | Non-Metallic | Smooth Matte |
| MP1210N        | MP1210N        | 305mm  | 254mm | 6.4mm | Non-Metallic | Smooth Matte |
| MP1412N        | MP1412N        | 356mm  | 305mm | 6.4mm | Non-Metallic | Smooth Matte |
| MP1614N        | MP1614N        | 406mm  | 356mm | 6.4mm | Non-Metallic | Smooth Matte |
| MP1816N        | MP1816N        | 457mm  | 406mm | 6.4mm | Non-Metallic | Smooth Matte |
| MP2016N        | MP2016N        | 508mm  | 406mm | 6.4mm | Non-Metallic | Smooth Matte |
| MP806N         | MP806N         | 203mm  | 152mm | 6.4mm | Non-Metallic | Smooth Matte |
| MP3024N        | MP3024N        | 762mm  | 610mm | 6.4mm | Non-Metallic | Smooth Matte |
| MP3030N        | MP3030N        | 762mm  | 762mm | 6.4mm | Non-Metallic | Smooth Matte |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**