

nVent CADDY New Product Introductions

Fall 2025

Our nVent CADDY team of experts take time to create solutions with the customer and their challenges in mind — as well as building code requirements, difficult project challenges, and trends in the current market. Hours of research, product development and engineering go into nVent CADDY products to help solve for several barriers in the electrical and datacom markets. Our new product additions and improved offerings are the culmination of ongoing feedback provided by installation contractors. The results are a testament to our dedication to overall project cost savings, quality and innovation.

Benefits of our new and improved nVent CADDY solutions include:



Tool-free Installation



Improved Productivity



Fast and Easy Installation



Designed for Electrical



Time & Cost Savings




Designed for In-Wall

CABLE/CONDUIT STUD ATTACHMENT, MULTIFUNCTION (CS816M)

Compliant in:




- Multifunction design allows for different securement combinations such as one EMT and up to two flexible conduit cables or three conduit cables
- Capable of securing EMT sizes spanning from ½ to 1 in
- Score marks to break off excess bracket
- Compliant with NEC® Article 358.30(A), which requires conduit support within 36 in of an electrical box
- Compliant with CEC Rule 12-1404, which requires conduit support within 1 m of an electrical box
- Compliant with CEC Rule 12-618, which requires support of armored cable within 300 mm (12 in) of an electrical box



Cable/Conduit to
Stud Attachment
(CS812, CS812D, CS16)

TELESCOPING RECESSED LIGHT MOUNTING BRACKET (TBRL24)

- Designed to be used with the nVent CADDY T-Grid Clip for Recessed Light Mounting Bracket for T-Grid Ceiling Applications
- For installation of differently sized lights between 4 and 8 in
- Increased flexibility for installation with multiple fixture points
- Sturdy and reliable bracket plate
- Features an additional open slot that contractors can utilize for easy reach-through installations
- Bracket is designed for easy visual, removing the need for hand measuring



Compatible with:



T-Grid Clip for
Recessed Light
Mounting Bracket
(RLTG)

T-GRID CLIP FOR RECESSED LIGHT MOUNTING BRACKET (RLTG)

- Designed to be used with the nVent CADDY Telescoping Recessed Light Mounting Bracket or nVent CADDY Heavy Duty Telescoping Bracket
- Intended for quick and easy alignment
- Drop wire attachment hole incorporated



Compatible with:




Telescoping
Recessed Light
Mounting Bracket
(TBRL24)



Heavy Duty
Telescoping Bracket
(TB1624HD)

ROD LOCK PREFABRICATED STRUT ASSEMBLY (CRLP##SSA12L##)

Compliant in:  

- Slot-to-slot configuration allows cartridges to adjust up to ¼ in on each end from the center of the slot
- Accommodates slight variation in rod-to-rod position of the trapeze
- Lock nut can easily be tightened without the use of tools
- Works with all accessories that fit standard A type strut channels

Compatible with:



Ladder Tray Clip
(LTC)

Application Image:




SN Series Nut
(SN37/SN50)



SNSW Flanged Nut
(SNSW37/SNSW50)





Square Channel Washer
(F##0000EG)



Rod Lock Strut Clip
(CRLSC37/CRLSC50)



LADDER TRAY CLIP (LTC)

Compliant in:  

- Single-piece design with hardware pre-installed to reduce components
- Simple and time-saving; just twist and drop the Ladder Tray Clip directly into the strut profile
- Works on ladder tray with up to ½ in flange thickness
- Hot-dip galvanized clamp and hardware for demanding environments
- Integrated clamping teeth for superior holding strength and load ratings

Compatible with:




Rod Lock
Prefabricated
Strut Assembly




Pyramid
H-Frame Kit
(PHK/PHKR)




Pyramid ST
Fixed Strut Support
(PSF##)



Pyramid ST
Bridge Assembly
(PSB##A)



Pyramid ST
Adjustable Strut
Support
(PSA)



PYRAMID POWER SWITCH MOUNT (PEKPSM)

- Mounts easily to 1 5/8 in strut or 1 1/4 in SCH pipe
- Can handle a wide range of power disconnect boxes
- Hot-dip galvanized construction for demanding environments



Compatible with:



Pyramid PEK
Wall Mount Support
(PEKWM)




nVent CADDY Pyramid Prefab H-Frame Configurator Software

- ✓ Digitally configure, price and quote prefabricated H-Frames
- ✓ Increase safety and efficiency during service runs
- ✓ Full project design and layout package available to reduce complexity



COMING SOON

NVENT CADDY WBT PERFORMANCE CABLE TRAY POLYMER INSERT, PERFORATED



- Prescored for specific securement applications
- Polymer insert rolls into the tray bottom
- Multiple color options to coordinate with cable tray selection
- Easily field configurable



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE