


Novastar Frame, Heavy-Duty



Aesthetic aluminum die-cast frame with 400 kg static load capacity. Aluminum extruded 19" upright bolted onto the frames.

CERTIFICATIONS



FEATURES

Static load-carrying capacity 400 kg

19" plane - 60 mm at front, 60 mm at rear

Al profile, RAL 7021, incl. grounding

SPECIFICATIONS

Frame Material:	Aluminum
Material:	Aluminum
Product Type:	Cabinet/Rack Frame

Table 1/2

Catalog Number	Rack Height	Height	Width	Depth	Package Quantity	Color
28230-056	12U	589mm	553mm	900mm	1	Black Grey
28230-189	12U	589mm	553mm	1000mm	1	Black Grey
28230-192	16U	767mm	553mm	900mm	1	Black Grey
28230-193	16U	767mm	553mm	1000mm	1	Black Grey
28230-196	20U	945mm	553mm	900mm	1	Black Grey
28230-197	20U	945mm	553mm	1000mm	1	Black Grey
28230-200	25U	1167mm	553mm	900mm	1	Black Grey
28230-201	25U	1167mm	553mm	1000mm	1	Black Grey
28230-204	34U	1567mm	553mm	900mm	1	Black Grey
28230-205	34U	1567mm	553mm	1000mm	1	Black Grey
28230-208	38U	1745mm	553mm	900mm	1	Black Grey
28230-209	38U	1745mm	553mm	1000mm	1	Black Grey
28230-212	43U	1967mm	553mm	900mm	1	Black Grey
28230-213	43U	1967mm	553mm	1000mm	1	Black Grey
28230-216	47U	2145mm	553mm	900mm	1	Black Grey
28230-217	47U	2145mm	553mm	1000mm	1	Black Grey
28230-310	16U	767mm	553mm	500mm	1	Black Grey
28230-314	20U	945mm	553mm	500mm	1	Black Grey

CatalogNumber	Rack Height	Height	Width	Depth	Package Quantity	Color
28230-319	25U	1167mm	553mm	500mm	1	Black Grey
28230-328	34U	1567mm	553mm	500mm	1	Black Grey
28230-332	38U	1745mm	553mm	500mm	1	Black Grey
28230-337	43U	1967mm	553mm	500mm	1	Black Grey
28230-341	47U	2145mm	553mm	500mm	1	Black Grey
28230-370	16U	767mm	553mm	600mm	1	Black Grey
28230-374	20U	945mm	553mm	600mm	1	Black Grey
28230-379	25U	1167mm	553mm	600mm	1	Black Grey
28230-388	34U	1567mm	553mm	600mm	1	Black Grey
28230-392	38U	1745mm	553mm	600mm	1	Black Grey
28230-397	43U	1967mm	553mm	600mm	1	Black Grey
28230-401	47U	2145mm	553mm	600mm	1	Black Grey
28230-430	16U	767mm	553mm	800mm	1	Black Grey
28230-434	20U	945mm	553mm	800mm	1	Black Grey
28230-439	25U	1167mm	553mm	800mm	1	Black Grey
28230-448	34U	1567mm	553mm	800mm	1	Black Grey
28230-452	38U	1745mm	553mm	800mm	1	Black Grey
28230-457	43U	1967mm	553mm	800mm	1	Black Grey

CatalogNumber	Rack Height	Height	Width	Depth	Package Quantity	Color
28230-461	47U	2145mm	553mm	800mm	1	Black Grey
28230-219	29U	1345mm	553mm	900mm	1	Black Grey
28230-220	29U	1345mm	553mm	1000mm	1	Black Grey
28230-323	29U	1345mm	553mm	500mm	1	Black Grey
28230-383	29U	1345mm	553mm	600mm	1	Black Grey
28230-443	29U	1345mm	553mm	800mm	1	Black Grey

Table 2/2					
Catalog Number	Color Code	Finish	Type	Certifications	Quick Ship
28230-056	RAL 7021	Powder Coated	Heavy Duty	RoHS	No
28230-189	RAL 7021	Powder Coated	Heavy Duty	RoHS	No
28230-192	RAL 7021	Powder Coated	Heavy Duty	RoHS	No
28230-193	RAL 7021	Powder Coated	Heavy Duty	RoHS	No
28230-196	RAL 7021	Powder Coated	Heavy Duty	RoHS	No
28230-197	RAL 7021	Powder Coated	Heavy Duty	RoHS	No
28230-200	RAL 7021	Powder Coated	Heavy Duty	RoHS	No
28230-201	RAL 7021	Powder Coated	Heavy Duty	RoHS	No
28230-204	RAL 7021	Powder Coated	Heavy Duty	RoHS	No
28230-205	RAL 7021	Powder Coated	Heavy Duty	RoHS	No
28230-208	RAL 7021	Powder Coated	Heavy Duty	RoHS	No

Catalog Number	Color Code	Finish	Type	Certifications	Quick Ship
28230-209	RAL 7021	Powder Coated	Heavy Duty	RoHS	No
28230-212	RAL 7021	Powder Coated	Heavy Duty	RoHS	No
28230-213	RAL 7021	Powder Coated	Heavy Duty	RoHS	No
28230-216	RAL 7021	Powder Coated	Heavy Duty	RoHS	No
28230-217	RAL 7021	Powder Coated	Heavy Duty	RoHS	No
28230-310	RAL 7021	Powder Coated	Heavy Duty	RoHS	No
28230-314	RAL 7021	Powder Coated	Heavy Duty	RoHS	No
28230-319	RAL 7021	Powder Coated	Heavy Duty	RoHS	No
28230-328	RAL 7021	Powder Coated	Heavy Duty	RoHS	No
28230-332	RAL 7021	Powder Coated	Heavy Duty	RoHS	No
28230-337	RAL 7021	Powder Coated	Heavy Duty	RoHS	No
28230-341	RAL 7021	Powder Coated	Heavy Duty	RoHS	No
28230-370	RAL 7021	Powder Coated	Heavy Duty	RoHS	No
28230-374	RAL 7021	Powder Coated	Heavy Duty	RoHS	No
28230-379	RAL 7021	Powder Coated	Heavy Duty	RoHS	No
28230-388	RAL 7021	Powder Coated	Heavy Duty	RoHS	No
28230-392	RAL 7021	Powder Coated	Heavy Duty	RoHS	No
28230-397	RAL 7021	Powder Coated	Heavy Duty	RoHS	No

Catalog Number	Color Code	Finish	Type	Certifications	Quick Ship
28230-401	RAL 7021	Powder Coated	Heavy Duty	RoHS	No
28230-430	RAL 7021	Powder Coated	Heavy Duty	RoHS	No
28230-434	RAL 7021	Powder Coated	Heavy Duty	RoHS	No
28230-439	RAL 7021	Powder Coated	Heavy Duty	RoHS	No
28230-448	RAL 7021	Powder Coated	Heavy Duty	RoHS	No
28230-452	RAL 7021	Powder Coated	Heavy Duty	RoHS	No
28230-457	RAL 7021	Powder Coated	Heavy Duty	RoHS	No
28230-461	RAL 7021	Powder Coated	Heavy Duty	RoHS	No
28230-219	RAL 7021	Powder Coated	Heavy Duty		No
28230-220	RAL 7021	Powder Coated	Heavy Duty		No
28230-323	RAL 7021	Powder Coated	Heavy Duty		No
28230-383	RAL 7021	Powder Coated	Heavy Duty		No
28230-443	RAL 7021	Powder Coated	Heavy Duty		No

ADDITIONAL PRODUCT DETAILS

Please order doors, rear panels, side panels, top cover assemblies, plinths, floors, shelves, slide rails and castors or adjustable feet separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE