

## ProLine 100-mm Solid Base



ProLine 100-mm Solid Base is installed at the bottom of the enclosure. Side gland plates and drill points for locating optional casters are included.

### FEATURES

---

EMC bases are finished with paint over plated surfaces

Side gland plates included

Castors not included, but drill points for installing them are

## SPECIFICATIONS

| Table 1/1      |                |                     |               |           |            |           |
|----------------|----------------|---------------------|---------------|-----------|------------|-----------|
| Catalog Number | Article Number | Material            | Finish        | Color     | Color Code | Thickness |
| PB1105         | 97770          | Mild Steel          | Powder Coated | Jet Black | RAL 9005   | 1.52mm    |
| PB1105HF       | 12959          | Mild Steel          | Powder Coated | Jet Black | RAL 9005   | 1.52mm    |
| PB1106         | 97780          | Mild Steel          | Powder Coated | Jet Black | RAL 9005   | 1.52mm    |
| PB1106SS       | 32009          | Stainless Steel 304 | Brushed       |           |            | 1.52mm    |
| PB1124         | 97800          | Mild Steel          | Powder Coated | Jet Black | RAL 9005   | 1.52mm    |
| PB1125         | 97810          | Mild Steel          | Powder Coated | Jet Black | RAL 9005   | 1.52mm    |
| PB1126         | 97820          | Mild Steel          | Powder Coated | Jet Black | RAL 9005   | 1.52mm    |
| PB1126SS       | 32029          | Stainless Steel 304 | Brushed       |           |            | 1.52mm    |
| PB1165         | 97840          | Mild Steel          | Powder Coated | Jet Black | RAL 9005   | 1.52mm    |
| PB1166         | 97850          | Mild Steel          | Powder Coated | Jet Black | RAL 9005   | 1.52mm    |
| PB145          | 25539          | Mild Steel          | Powder Coated | Jet Black | RAL 9005   | 1.52mm    |
| PB146          | 25549          | Mild Steel          | Powder Coated | Jet Black | RAL 9005   | 1.52mm    |
| PB164          | 97650          | Mild Steel          | Powder Coated | Jet Black | RAL 9005   | 1.52mm    |
| PB165          | 97660          | Mild Steel          | Powder Coated | Jet Black | RAL 9005   | 1.52mm    |
| PB165HF        | 12849          | Mild Steel          | Powder Coated | Jet Black | RAL 9005   | 1.52mm    |
| PB166          | 97670          | Mild Steel          | Powder Coated | Jet Black | RAL 9005   | 1.52mm    |
| PB166SS        | 31969          | Stainless Steel 304 | Brushed       |           |            | 1.52mm    |
| PB176          | 97690          | Mild Steel          | Powder Coated | Jet Black | RAL 9005   | 1.52mm    |
| PB184          | 97720          | Mild Steel          | Powder Coated | Jet Black | RAL 9005   | 1.52mm    |

| Catalog Number | Article Number | Material               | Finish        | Color     | Color Code | Thickness |
|----------------|----------------|------------------------|---------------|-----------|------------|-----------|
| PB184HF        | 12909          | Mild Steel             | Powder Coated | Jet Black | RAL 9005   | 1.52mm    |
| PB185          | 97730          | Mild Steel             | Powder Coated | Jet Black | RAL 9005   | 1.52mm    |
| PB185HF        | 12919          | Mild Steel             | Powder Coated | Jet Black | RAL 9005   | 1.52mm    |
| PB186          | 97740          | Mild Steel             | Powder Coated | Jet Black | RAL 9005   | 1.52mm    |
| PB1108         | 97790          | Mild Steel             | Powder Coated | Jet Black | RAL 9005   | 1.9mm     |
| PB1108HF       | 12979          | Mild Steel             | Powder Coated | Jet Black | RAL 9005   | 1.9mm     |
| PB1108SS       | 32019          | Stainless Steel<br>304 | Brushed       |           |            | 1.9mm     |
| PB1128         | 97830          | Mild Steel             | Powder Coated | Jet Black | RAL 9005   | 1.9mm     |
| PB1128SS       | 32039          | Stainless Steel<br>304 | Brushed       |           |            | 1.9mm     |
| PB1168         | 97860          | Mild Steel             | Powder Coated | Jet Black | RAL 9005   | 1.9mm     |
| PB168          | 97680          | Mild Steel             | Powder Coated | Jet Black | RAL 9005   | 1.9mm     |
| PB168HF        | 12869          | Mild Steel             | Powder Coated | Jet Black | RAL 9005   | 1.9mm     |
| PB168SS        | 31979          | Stainless Steel<br>304 | Brushed       |           |            | 1.9mm     |
| PB178          | 97700          | Mild Steel             | Powder Coated | Jet Black | RAL 9005   | 1.9mm     |
| PB179HF        | 12899          | Mild Steel             | Powder Coated | Jet Black | RAL 9005   | 1.9mm     |
| PB188          | 97750          | Mild Steel             | Powder Coated | Jet Black | RAL 9005   | 1.9mm     |
| PB189          | 97760          | Mild Steel             | Powder Coated | Jet Black | RAL 9005   | 1.9mm     |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**