

# Cable Eye for 19" Front Panel

Simple to fit cable eyes into 19" front panel for cable eyes.



## CERTIFICATIONS



## FEATURES

Simple to fit cable eyes into 19" front panel for cable eyes. Insert cable eyes into frontpanel and rotate them 45°

## SPECIFICATIONS

**Width (W):** 30mm  
**Product Type:** Cable Eye  
**Works With:** Varistar CP

Table 1/2


| Catalog Number | Material         | Depth (D) | Package Quantity | Color | Finish      | Height (H) |
|----------------|------------------|-----------|------------------|-------|-------------|------------|
| 60118-473      | Steel, Polyamide | 85.3mm    | 5                |       | Zinc Plated | 44mm       |
| 60118-457      | Steel, Polyamide | 120.8mm   | 5                |       | Zinc Plated | 44mm       |
| 60118-459      | Polyamide        | 103.2mm   | 5                | Black |             | 42.5mm     |

| CatalogNumber | Material            | Depth (D) | Package Quantity | Color | Finish      | Height (H) |
|---------------|---------------------|-----------|------------------|-------|-------------|------------|
| 60118-458     | Polyamide           | 59mm      | 5                | Black |             | 42.5mm     |
| 60118-474     | Steel,<br>Polyamide | 120.3mm   | 5                |       | Zinc Plated | 44mm       |

Table 2/2

| Catalog Number | Length (L) | Cable Type | Quick Ship |
|----------------|------------|------------|------------|
| 60118-473      | 80mm       | Double     | No         |
| 60118-457      | 115mm      | Single     | No         |
| 60118-459      | 100mm      | Single     | No         |
| 60118-458      | 55mm       | Single     | No         |
| 60118-474      | 115mm      | Double     | No         |

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**