

# Varistar Colocation Cabinet, RAL 7021

## Data Solutions



Colocation cabinets with 2, 3 or 4 divider units in RAL 7021 to accommodate servers while separating access and cabling of the compartments.

### CERTIFICATIONS



### FEATURES

Colocation cabinets with compartments

Flexible cabling, possible from above, below, left or right (data and power cables can be run separately)

Multi-point door latch

Perforated doors

Protection class IP 20

Color RAL 7021 (black grey)

### SPECIFICATIONS

**Product Type:** Rack

**Frame Material:** Steel

Table 1/3

| Catalog Number | Rack Height | Height | Cladding Material | Frame Color | Width | Frame Color Code |
|----------------|-------------|--------|-------------------|-------------|-------|------------------|
|----------------|-------------|--------|-------------------|-------------|-------|------------------|

|           |     |        |       |            |       |          |
|-----------|-----|--------|-------|------------|-------|----------|
| 10130-202 | 40U | 2000mm | Steel | Black Grey | 600mm | RAL 7021 |
| 10130-203 | 39U | 2000mm | Steel | Black Grey | 600mm | RAL 7021 |
| 10130-204 | 40U | 2000mm | Steel | Black Grey | 600mm | RAL 7021 |
| 10130-205 | 40U | 2000mm | Steel | Black Grey | 800mm | RAL 7021 |
| 10130-206 | 39U | 2000mm | Steel | Black Grey | 800mm | RAL 7021 |
| 10130-207 | 40U | 2000mm | Steel | Black Grey | 800mm | RAL 7021 |
| 10130-208 | 44U | 2200mm | Steel | Black Grey | 600mm | RAL 7021 |
| 10130-209 | 45U | 2200mm | Steel | Black Grey | 600mm | RAL 7021 |
| 10130-210 | 44U | 2200mm | Steel | Black Grey | 600mm | RAL 7021 |
| 10130-211 | 44U | 2200mm | Steel | Black Grey | 800mm | RAL 7021 |
| 10130-212 | 45U | 2200mm | Steel | Black Grey | 800mm | RAL 7021 |
| 10130-213 | 44U | 2200mm | Steel | Black Grey | 800mm | RAL 7021 |
| 10130-214 | 40U | 2000mm | Steel | Black Grey | 600mm | RAL 7021 |
| 10130-215 | 39U | 2000mm | Steel | Black Grey | 600mm | RAL 7021 |
| 10130-216 | 40U | 2000mm | Steel | Black Grey | 600mm | RAL 7021 |
| 10130-217 | 40U | 2000mm | Steel | Black Grey | 800mm | RAL 7021 |
| 10130-218 | 39U | 2000mm | Steel | Black Grey | 800mm | RAL 7021 |
| 10130-219 | 40U | 2000mm | Steel | Black Grey | 800mm | RAL 7021 |
| 10130-220 | 44U | 2200mm | Steel | Black Grey | 600mm | RAL 7021 |

|           |     |        |       |            |       |          |
|-----------|-----|--------|-------|------------|-------|----------|
| 10130-221 | 45U | 2200mm | Steel | Black Grey | 600mm | RAL 7021 |
| 10130-222 | 44U | 2200mm | Steel | Black Grey | 600mm | RAL 7021 |
| 10130-223 | 44U | 2200mm | Steel | Black Grey | 800mm | RAL 7021 |
| 10130-224 | 45U | 2200mm | Steel | Black Grey | 800mm | RAL 7021 |
| 10130-225 | 44U | 2200mm | Steel | Black Grey | 800mm | RAL 7021 |
| 10130-257 | 45U | 2450mm | Steel | Black Grey | 600mm | RAL 7021 |
| 10130-258 | 48U | 2450mm | Steel | Black Grey | 600mm | RAL 7021 |
| 10130-259 | 48U | 2450mm | Steel | Black Grey | 600mm | RAL 7021 |
| 10130-260 | 45U | 2450mm | Steel | Black Grey | 800mm | RAL 7021 |
| 10130-261 | 48U | 2450mm | Steel | Black Grey | 800mm | RAL 7021 |
| 10130-262 | 48U | 2450mm | Steel | Black Grey | 800mm | RAL 7021 |
| 10130-269 | 45U | 2450mm | Steel | Black Grey | 600mm | RAL 7021 |
| 10130-270 | 48U | 2450mm | Steel | Black Grey | 600mm | RAL 7021 |
| 10130-271 | 48U | 2450mm | Steel | Black Grey | 600mm | RAL 7021 |
| 10130-272 | 45U | 2450mm | Steel | Black Grey | 800mm | RAL 7021 |
| 10130-273 | 48U | 2450mm | Steel | Black Grey | 800mm | RAL 7021 |
| 10130-274 | 48U | 2450mm | Steel | Black Grey | 800mm | RAL 7021 |

Table 2/3

| Catalog Number | Cladding Color | Cladding Color Code | Depth | Package Quantity | Number of Compartments | Finish |
|----------------|----------------|---------------------|-------|------------------|------------------------|--------|
|----------------|----------------|---------------------|-------|------------------|------------------------|--------|

|           |            |          |        |   |   |               |
|-----------|------------|----------|--------|---|---|---------------|
| 10130-202 | Black Grey | RAL 7021 | 1000mm | 1 | 2 | Powder Coated |
| 10130-203 | Black Grey | RAL 7021 | 1000mm | 1 | 3 | Powder Coated |
| 10130-204 | Black Grey | RAL 7021 | 1000mm | 1 | 4 | Powder Coated |
| 10130-205 | Black Grey | RAL 7021 | 1000mm | 1 | 2 | Powder Coated |
| 10130-206 | Black Grey | RAL 7021 | 1000mm | 1 | 3 | Powder Coated |
| 10130-207 | Black Grey | RAL 7021 | 1000mm | 1 | 4 | Powder Coated |
| 10130-208 | Black Grey | RAL 7021 | 1000mm | 1 | 2 | Powder Coated |
| 10130-209 | Black Grey | RAL 7021 | 1000mm | 1 | 3 | Powder Coated |
| 10130-210 | Black Grey | RAL 7021 | 1000mm | 1 | 4 | Powder Coated |
| 10130-211 | Black Grey | RAL 7021 | 1000mm | 1 | 2 | Powder Coated |
| 10130-212 | Black Grey | RAL 7021 | 1000mm | 1 | 3 | Powder Coated |
| 10130-213 | Black Grey | RAL 7021 | 1000mm | 1 | 4 | Powder Coated |
| 10130-214 | Black Grey | RAL 7021 | 1200mm | 1 | 2 | Powder Coated |
| 10130-215 | Black Grey | RAL 7021 | 1200mm | 1 | 3 | Powder Coated |
| 10130-216 | Black Grey | RAL 7021 | 1200mm | 1 | 4 | Powder Coated |
| 10130-217 | Black Grey | RAL 7021 | 1200mm | 1 | 2 | Powder Coated |
| 10130-218 | Black Grey | RAL 7021 | 1200mm | 1 | 3 | Powder Coated |
| 10130-219 | Black Grey | RAL 7021 | 1200mm | 1 | 4 | Powder Coated |
| 10130-220 | Black Grey | RAL 7021 | 1200mm | 1 | 2 | Powder Coated |

|           |            |          |        |   |   |               |
|-----------|------------|----------|--------|---|---|---------------|
| 10130-221 | Black Grey | RAL 7021 | 1200mm | 1 | 3 | Powder Coated |
| 10130-222 | Black Grey | RAL 7021 | 1200mm | 1 | 4 | Powder Coated |
| 10130-223 | Black Grey | RAL 7021 | 1200mm | 1 | 2 | Powder Coated |
| 10130-224 | Black Grey | RAL 7021 | 1200mm | 1 | 3 | Powder Coated |
| 10130-225 | Black Grey | RAL 7021 | 1200mm | 1 | 4 | Powder Coated |
| 10130-257 | Black Grey | RAL 7021 | 1000mm | 1 | 2 | Powder Coated |
| 10130-258 | Black Grey | RAL 7021 | 1000mm | 1 | 3 | Powder Coated |
| 10130-259 | Black Grey | RAL 7021 | 1000mm | 1 | 4 | Powder Coated |
| 10130-260 | Black Grey | RAL 7021 | 1000mm | 1 | 2 | Powder Coated |
| 10130-261 | Black Grey | RAL 7021 | 1000mm | 1 | 3 | Powder Coated |
| 10130-262 | Black Grey | RAL 7021 | 1000mm | 1 | 4 | Powder Coated |
| 10130-269 | Black Grey | RAL 7021 | 1200mm | 1 | 2 | Powder Coated |
| 10130-270 | Black Grey | RAL 7021 | 1200mm | 1 | 3 | Powder Coated |
| 10130-271 | Black Grey | RAL 7021 | 1200mm | 1 | 4 | Powder Coated |
| 10130-272 | Black Grey | RAL 7021 | 1200mm | 1 | 2 | Powder Coated |
| 10130-273 | Black Grey | RAL 7021 | 1200mm | 1 | 3 | Powder Coated |
| 10130-274 | Black Grey | RAL 7021 | 1200mm | 1 | 4 | Powder Coated |

| Table 3/3      |          |             |
|----------------|----------|-------------|
| Catalog Number | Material | Static Load |
| 10130-202      | Steel    | 800kg       |

| Catalog Number | Material | Static Load |
|----------------|----------|-------------|
| 10130-203      | Steel    | 800kg       |
| 10130-204      | Steel    | 800kg       |
| 10130-205      | Steel    | 800kg       |
| 10130-206      | Steel    | 800kg       |
| 10130-207      | Steel    | 800kg       |
| 10130-208      | Steel    | 800kg       |
| 10130-209      | Steel    | 800kg       |
| 10130-210      | Steel    | 800kg       |
| 10130-211      | Steel    | 800kg       |
| 10130-212      | Steel    | 800kg       |
| 10130-213      | Steel    | 800kg       |
| 10130-214      | Steel    | 800kg       |
| 10130-215      | Steel    | 800kg       |
| 10130-216      | Steel    | 800kg       |
| 10130-217      | Steel    | 800kg       |
| 10130-218      | Steel    | 800kg       |
| 10130-219      | Steel    | 800kg       |
| 10130-220      | Steel    | 800kg       |

| Catalog Number | Material | Static Load |
|----------------|----------|-------------|
| 10130-221      | Steel    | 800kg       |
| 10130-222      | Steel    | 800kg       |
| 10130-223      | Steel    | 800kg       |
| 10130-224      | Steel    | 800kg       |
| 10130-225      | Steel    | 800kg       |
| 10130-257      | Steel    | 800kg       |
| 10130-258      | Steel    | 800kg       |
| 10130-259      | Steel    | 800kg       |
| 10130-260      | Steel    | 800kg       |
| 10130-261      | Steel    | 800kg       |
| 10130-262      | Steel    | 800kg       |
| 10130-269      | Steel    | 800kg       |
| 10130-270      | Steel    | 800kg       |
| 10130-271      | Steel    | 800kg       |
| 10130-272      | Steel    | 800kg       |
| 10130-273      | Steel    | 800kg       |
| 10130-274      | Steel    | 800kg       |

## ADDITIONAL PRODUCT DETAILS

---

Side panel must be ordered separately. For suitable cable panel see Accessories.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**