


Novastar Frame, Slim-Line

Power Utilities



Aesthetic aluminum die-cast frame with 200kg static load capacity. Aluminum extruded 19" upright bolted onto the frames.

CERTIFICATIONS



FEATURES

Static load-carrying capacity 200 kg

19" plane - 33 mm at front, 60 mm at rear

Al profile, RAL 7021, incl. grounding

SPECIFICATIONS

Table 1/2

Catalog Number	Rack Height	Height	Width	Depth	Color	Color Code
----------------	-------------	--------	-------	-------	-------	------------

28230-001	6 U	323 mm	553 mm	500 mm	Black Grey	RAL 7021
28230-060	6 U	323 mm	553 mm	600 mm	Black Grey	RAL 7021
28230-063	9 U	456 mm	553 mm	600 mm	Black Grey	RAL 7021
28230-004	9 U	456 mm	553 mm	500 mm	Black Grey	RAL 7021
28230-126	12 U	589 mm	553 mm	800 mm	Black Grey	RAL 7021
28230-007	12 U	589 mm	553 mm	500 mm	Black Grey	RAL 7021
28230-054	12 U	589 mm	553 mm	900 mm	Black Grey	RAL 7021
28230-055	12 U	589 mm	553 mm	1000 mm	Black Grey	RAL 7021
28230-066	12 U	589 mm	553 mm	600 mm	Black Grey	RAL 7021
28230-190	16 U	767 mm	553 mm	900 mm	Black Grey	RAL 7021
28230-011	16 U	767 mm	553 mm	500 mm	Black Grey	RAL 7021
28230-191	16 U	767 mm	553 mm	1000 mm	Black Grey	RAL 7021
28230-130	16 U	767 mm	553 mm	800 mm	Black Grey	RAL 7021
28230-070	16 U	767 mm	553 mm	600 mm	Black Grey	RAL 7021
28230-015	20 U	945 mm	553 mm	500 mm	Black Grey	RAL 7021
28230-134	20 U	945 mm	553 mm	800 mm	Black Grey	RAL 7021
28230-194	20 U	945 mm	553 mm	900 mm	Black Grey	RAL 7021
28230-074	20 U	945 mm	553 mm	600 mm	Black Grey	RAL 7021
28230-195	20 U	945 mm	553 mm	1000 mm	Black Grey	RAL 7021

28230-139	25 U	1167 mm	553 mm	800 mm	Black Grey	RAL 7021
28230-198	25 U	1167 mm	553 mm	900 mm	Black Grey	RAL 7021
28230-079	25 U	1167 mm	553 mm	600 mm	Black Grey	RAL 7021
28230-199	25 U	1167 mm	553 mm	1000 mm	Black Grey	RAL 7021
28230-020	25 U	1167 mm	553 mm	500 mm	Black Grey	RAL 7021
28230-202	34 U	1567 mm	553 mm	900 mm	Black Grey	RAL 7021
28230-148	34 U	1567 mm	553 mm	800 mm	Black Grey	RAL 7021
28230-088	34 U	1567 mm	553 mm	600 mm	Black Grey	RAL 7021
28230-203	34 U	1567 mm	553 mm	1000 mm	Black Grey	RAL 7021
28230-029	34 U	1567 mm	553 mm	500 mm	Black Grey	RAL 7021
28230-152	38 U	1745 mm	553 mm	800 mm	Black Grey	RAL 7021
28230-206	38 U	1745 mm	553 mm	900 mm	Black Grey	RAL 7021
28230-033	38 U	1745 mm	553 mm	500 mm	Black Grey	RAL 7021
28230-207	38 U	1745 mm	553 mm	1000 mm	Black Grey	RAL 7021
28230-092	38 U	1745 mm	553 mm	600 mm	Black Grey	RAL 7021
28230-210	43 U	1967 mm	553 mm	900 mm	Black Grey	RAL 7021
28230-097	43 U	1967 mm	553 mm	600 mm	Black Grey	RAL 7021
28230-157	43 U	1967 mm	553 mm	800 mm	Black Grey	RAL 7021
28230-211	43 U	1967 mm	553 mm	1000 mm	Black Grey	RAL 7021

28230-048	43 U	1967 mm	553 mm	500 mm	Black Grey	RAL 7021
28230-162	47 U	2145 mm	553 mm	800 mm	Black Grey	RAL 7021
28230-214	47 U	2145 mm	553 mm	900 mm	Black Grey	RAL 7021
28230-101	47 U	2145 mm	553 mm	600 mm	Black Grey	RAL 7021
28230-042	47 U	2145 mm	553 mm	500 mm	Black Grey	RAL 7021
28230-215	47 U	2145 mm	553 mm	1000 mm	Black Grey	RAL 7021

Table 2/2				
Catalog Number	Frame Material	Product Type	Static Load	Type
28230-001	Aluminum	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-060	Aluminum	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-063	Aluminum	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-004	Aluminum	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-126	Aluminum	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-007	Aluminum	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-054	Aluminum	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-055	Aluminum	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-066	Aluminum	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-190	Aluminum	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-011	Aluminum	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-191	Aluminum	Cabinet/Rack Frame	200 kgf	Slim-Line

Catalog Number	Frame Material	Product Type	Static Load	Type
28230-130	Aluminum	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-070	Aluminum	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-015	Aluminum	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-134	Aluminum	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-194	Aluminum	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-074	Aluminum	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-195	Aluminum	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-139	Aluminum	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-198	Aluminum	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-079	Aluminum	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-199	Aluminum	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-020	Aluminum	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-202	Aluminum	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-148	Aluminum	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-088	Aluminum	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-203	Aluminum	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-029	Aluminum	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-152	Aluminum	Cabinet/Rack Frame	200 kgf	Slim-Line

Catalog Number	Frame Material	Product Type	Static Load	Type
28230-206	Aluminum	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-033	Aluminum	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-207	Aluminum	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-092	Aluminum	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-210	Aluminum	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-097	Aluminum	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-157	Aluminum	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-211	Aluminum	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-048	Aluminum	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-162	Aluminum	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-214	Aluminum	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-101	Aluminum	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-042	Aluminum	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-215	Aluminum	Cabinet/Rack Frame	200 kgf	Slim-Line

ADDITIONAL PRODUCT DETAILS

Please order doors, rear panels, side panels, top cover assemblies, plinths, floors, shelves, slide rails and castors or adjustable feet separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE