


# Disconnecting Link with Enclosure for Cable



## FEATURES

Allows for quick and easy disconnection of the earthing system to facilitate testing of the earth in isolation

High conductivity, hard drawn, electrolytic tough pitch copper per EN 13601

Includes stainless steel 304 enclosure, rubber dustproof, halogen-free polyamide insulators, stainless steel hardware

Compression straight lug: according to DIN46235 standard

Rubber gland for cable connection

8 microns tinned finish according to ASTM B545 Service Class "C"

## SPECIFICATIONS

Table 1/3

Catalog Number	Material	Finish	A	Diameter (Ø)	Height (H)	Thickness (T)
DLCBX95	Stainless Steel 304 (EN 1.4301), Copper	Bare	90 mm	20 mm	66.5 mm	4 mm
DLTBX95	Stainless Steel 304 (EN 1.4301), Tinned Copper	Tinned	90 mm	20 mm	66.5 mm	4 mm

Table 2/3

Catalog Number	Thread Size (TS)	Length 1 (L1)	Length 2 (L2)	Length 3 (L3)	Length 4 (L4)	Width 1 (W1)
DLCBX95	M8	125 mm	230 mm	210mm	160 mm	40 mm


CatalogNumber	Thread Size (TS)	Length 1 (L1)	Length 2 (L2)	Length 3 (L3)	Length 4 (L4)	Width 1 (W1)
DLTBX95	M8	125 mm	230 mm	210mm	160 mm	40 mm

Table 3/3			
Catalog Number	Width 2 (W2)	Width 3 (W3)	Unit Weight
DLCBX95	150 mm	170mm	1.45 kg
DLTBX95	150 mm	170mm	1.45 kg

### ADDITIONAL PRODUCT DETAILS

Available cable size ≤ 95 mm².

### DIAGRAMS



### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**