

# Mounting Plates Wall Mounted Enclosures, AMP



The steel mounting plate contributes to speeding up the assembly of the enclosure, since it can be machined easily and equipped with components before being mounted.

## FEATURES

---

Description: Steel mounting plate for wall mounted enclosures. All sizes from 800 mm and above are strengthened by folded edges. By using the AMG accessory, the mounting plate position can be adjusted to any depth. This accessory is not suitable for the AFS range of enclosures, please refer to the replacement and spare parts catalogue.

Material: Galvanized steel.

Pack quantity: 1 piece.

## SPECIFICATIONS

**Thickness:** 2mm  
**Finish:** Galvanized  
**Material:** Mild Steel

Table 1/1

| Catalog Number | Article Number | Height | Width | Depth | Panel Size  | Enclosure Material |
|----------------|----------------|--------|-------|-------|-------------|--------------------|
| AMP02020       | AMP02020       | 200mm  | 199mm | 2mm   | 170 x 150mm | Mild Steel         |
| AMP02520       | AMP02520       | 250mm  | 199mm | 2mm   | 220 x 150mm | Mild Steel         |
| AMP02525       | AMP02525       | 250mm  | 249mm | 2mm   | 220 x 200mm | Mild Steel         |
| AMP03025       | AMP03025       | 300mm  | 249mm | 2mm   | 270 x 200mm | Mild Steel         |
| AMP03030       | AMP03030       | 300mm  | 299mm | 2mm   | 270 x 250mm | Mild Steel         |
| AMP03040       | AMP03040       | 300mm  | 400mm | 2mm   | 270 x 350mm | Mild Steel         |
| AMP03060       | AMP03060       | 300mm  | 599mm | 2mm   | 270 x 550mm | Mild Steel         |
| AMP03080       | AMP03080       | 300mm  | 799mm | 2mm   | 270 x 750mm | Mild Steel         |
| AMP03525       | AMP03525       | 350mm  | 249mm | 2mm   | 320 x 200mm | Mild Steel         |
| AMP04030       | AMP04030       | 400mm  | 299mm | 2mm   | 370 x 250mm | Mild Steel         |
| AMP04040       | AMP04040       | 400mm  | 400mm | 2mm   | 370 x 350mm | Mild Steel         |
| AMP04050       | AMP04050       | 400mm  | 500mm | 2mm   | 370 x 450mm | Mild Steel         |
| AMP04060       | AMP04060       | 400mm  | 599mm | 2mm   | 370 x 550mm | Mild Steel         |
| AMP05030       | AMP05030       | 500mm  | 299mm | 2mm   | 470 x 250mm | Mild Steel         |
| AMP05040       | AMP05040       | 500mm  | 350mm | 2mm   | 470 x 350mm | Mild Steel         |
| AMP05050       | AMP05050       | 500mm  | 500mm | 2mm   | 470 x 450mm | Mild Steel         |

| Catalog Number | Article Number | Height | Width  | Depth | Panel Size    | EnclosureMaterial |
|----------------|----------------|--------|--------|-------|---------------|-------------------|
| AMP06040       | AMP06040       | 600mm  | 400mm  | 2mm   | 570 x 350mm   | Mild Steel        |
| AMP06050       | AMP06050       | 600mm  | 500mm  | 2mm   | 570 x 450mm   | Mild Steel        |
| AMP06060       | AMP06060       | 600mm  | 599mm  | 2mm   | 570 x 550mm   | Mild Steel        |
| AMP06080       | AMP06080       | 600mm  | 799mm  | 2mm   | 570 x 750mm   | Mild Steel        |
| AMP07050       | AMP07050       | 700mm  | 500mm  | 2mm   | 670 x 450mm   | Mild Steel        |
| AMP10100       | AMP10100       | 1000mm | 999mm  | 12mm  | 970 x 950mm   | Mild Steel        |
| AMP10120       | AMP10120       | 1000mm | 1199mm | 12mm  | 970 x 950mm   | Mild Steel        |
| AMP12120       | AMP12120       | 1200mm | 1199mm | 12mm  | 1170 x 1150mm | Mild Steel        |
| AMP03100       | AMP03100       | 300mm  | 999mm  | 12mm  | 270 x 950mm   | Mild Steel        |
| AMP03120       | AMP03120       | 300mm  | 1199mm | 12mm  | 270 x 1150mm  | Mild Steel        |
| AMP08040       | AMP08040       | 800mm  | 400mm  | 12mm  | 770 x 350mm   | Mild Steel        |
| AMP08060       | AMP08060       | 800mm  | 599mm  | 12mm  | 770 x 550mm   | Mild Steel        |
| AMP08080       | AMP08080       | 800mm  | 799mm  | 12mm  | 770 x 750mm   | Mild Steel        |
| AMP08120       | AMP08120       | 800mm  | 1199mm | 12mm  | 770 x 1150mm  | Mild Steel        |
| AMP10060       | AMP10060       | 1000mm | 599mm  | 12mm  | 970 x 550mm   | Mild Steel        |
| AMP10080       | AMP10080       | 1000mm | 799mm  | 12mm  | 970 x 750mm   | Mild Steel        |
| AMP12060       | AMP12060       | 1200mm | 599mm  | 12mm  | 1170 x 550mm  | Mild Steel        |
| AMP12080       | AMP12080       | 1200mm | 799mm  | 12mm  | 1170 x 750mm  | Mild Steel        |
| AMP12100       | AMP12100       | 1200mm | 999mm  | 12mm  | 1170 x 950mm  | Mild Steel        |
| AMP14100       | AMP14100       | 1400mm | 999mm  | 12mm  | 1370 x 950mm  | Mild Steel        |

## ADDITIONAL PRODUCT DETAILS

---

Not suitable for AFS.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**