

# Rubber Hanger



The Vibration Isolation Hanger line from nVent CADDY is used to support suspended objects or structural elements to effectively dampen potential vibration and noise transmission to a building structure. Hangers are typically mounted in ceilings where there are no lateral loads or changes in operating weight and hold suspended piping, ductwork, fans, and equipment.

## FEATURES

Used to suspend equipment, HVAC systems and piping

Powder coated steel housing

Rubber element prevents metal-on metal contact between threaded rod and bracket

## SPECIFICATIONS

Table 1/1

Catalog Number	Article Number	Length	Width	Height	Rod Size	Ultimate Static Load
VIBDDRHA100	801401	50.8mm	57.15mm	76.2mm	12.7	445N
VIBDDRHA015	801398	50.8mm	57.15mm	76.2mm	12.7	67N
VIBDDRHA030	801399	50.8mm	57.15mm	76.2mm	12.7	134N
VIBDDRHA060	801400	50.8mm	57.15mm	76.2mm	12.7	267N
VIBDDRHB150	801402	57.15mm	76.2mm	114.3mm	15.88	668N
VIBDDRHB300	801404	57.15mm	76.2mm	114.3mm	15.88	1335N
VIBDDRHC800	801407	88.9mm	101.6mm	152.4mm	15.88	3559N

CatalogNumber	Article Number	Length	Width	Height	Rod Size	Ultimate Static Load
VIBDDRHB400	801405	57.15mm	76.2mm	114.3mm	15.88	1780N
VIBDDRHB200	801403	57.15mm	76.2mm	114.3mm	15.88	890N
VIBDDRHC600	801406	88.9mm	101.6mm	152.4mm	15.88	2669N
VIBDDRHC1500	801409	101.6mm	114.3mm	152.4mm	19.05	6672N
VIBDDRHC2000	801410	101.6mm	114.3mm	152.4mm	19.05	8896N
VIBDDRHC1000	801408	101.6mm	114.3mm	152.4mm	19.05	4448N

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

### Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

### Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

### APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**

