


# AMC Pull-Handle Mechanism, AMC.0 R2.0



Handle mechanism AMC.0 Rev. 2.0, MTCA.1 and MTCA.4 Modules.

## CERTIFICATIONS



## FEATURES

Complete pull-handle mechanism, designed for microswitch activation (hot-swap), includes light pipe

For all nVent SCHROFF AdvancedMC modules

## SPECIFICATIONS

**Type:** Extractor

**Product Type:** Handle

Table 1/2

| Catalog Number | Design Feature | Material      | Handle Type     | Package Quantity | Flammability Rating | Color |
|----------------|----------------|---------------|-----------------|------------------|---------------------|-------|
| 20849-151      | Compact        | Polycarbonate | Single Compact  | 1                | UL® 94V-0           | Black |
| 20849-152      | Mid-Size       | Polycarbonate | Single Mid-Size | 1                | UL® 94V-0           | Black |
| 20849-155      | Mid-Size       | Polycarbonate | Double Mid-Size | 1                | UL® 94V-0           | Black |

| CatalogNumber | Design Feature | Material      | Handle Type      | Package Quantity | Flammability Rating | Color |
|---------------|----------------|---------------|------------------|------------------|---------------------|-------|
| 20849-153     | Full-Size      | Polycarbonate | Single Full-Size | 1                | UL® 94V-0           | Black |
| 20849-156     | Full-Size      | Polycarbonate | Double Full-Size | 1                | UL® 94V-0           | Black |

Table 2/2

| Catalog Number | Works With       | Quick Ship |
|----------------|------------------|------------|
| 20849-151      | MicroTCA Systems | No         |
| 20849-152      | MicroTCA Systems | No         |
| 20849-155      | MicroTCA Systems | No         |
| 20849-153      | MicroTCA Systems | No         |
| 20849-156      | MicroTCA Systems | No         |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**