

# Varistar CP Rear Panel, Screw Fixed

## Data Solutions



Cabinets have rear panels well screwed to the frame to have maximum contact with the gasket.

### FEATURES

Screw fixed, Robust and Single person mountable Side Panel

Rear panel without grounding kit

### SPECIFICATIONS

**Product Type:** Cabinet/Rack Panel

**Material:** Steel

Table 1/2

| Catalog Number | Rack Height | Height | Width | Protection Rating | Package Quantity | Color      |
|----------------|-------------|--------|-------|-------------------|------------------|------------|
| 21630-122      | 42U         | 2000mm | 600mm | IP20              | 1                | Black Grey |
| 21630-123      | 47U         | 2200mm | 600mm | IP20              | 1                | Black Grey |
| 21630-124      | 52U         | 2450mm | 600mm | IP20              | 1                | Black Grey |
| 21630-125      | 42U         | 2000mm | 800mm | IP20              | 1                | Black Grey |
| 21630-126      | 47U         | 2200mm | 800mm | IP20              | 1                | Black Grey |

| CatalogNumber | Rack Height | Height | Width | Protection Rating | Package Quantity | Color      |
|---------------|-------------|--------|-------|-------------------|------------------|------------|
| 21630-127     | 52U         | 2450mm | 800mm | IP20              | 1                | Black Grey |
| 21630-198     | 24U         | 1200mm | 600mm | IP55              | 1                | Black Grey |
| 21630-199     | 29U         | 1400mm | 600mm | IP55              | 1                | Black Grey |
| 21630-200     | 33U         | 1600mm | 600mm | IP55              | 1                | Black Grey |
| 21630-201     | 38U         | 1800mm | 600mm | IP55              | 1                | Black Grey |
| 21630-202     | 42U         | 2000mm | 600mm | IP55              | 1                | Black Grey |
| 21630-203     | 47U         | 2200mm | 600mm | IP55              | 1                | Black Grey |
| 21630-204     | 24U         | 1200mm | 800mm | IP55              | 1                | Black Grey |
| 21630-205     | 29U         | 1400mm | 800mm | IP55              | 1                | Black Grey |
| 21630-206     | 33U         | 1600mm | 800mm | IP55              | 1                | Black Grey |
| 21630-207     | 38U         | 1800mm | 800mm | IP55              | 1                | Black Grey |
| 21630-208     | 42U         | 2000mm | 800mm | IP55              | 1                | Black Grey |
| 21630-209     | 47U         | 2200mm | 800mm | IP55              | 1                | Black Grey |
| 21630-384     | 24U         | 1200mm | 600mm | IP20              | 1                | Black Grey |
| 21630-385     | 24U         | 1200mm | 800mm | IP20              | 1                | Black Grey |
| 21630-386     | 29U         | 1400mm | 600mm | IP20              | 1                | Black Grey |
| 21630-387     | 29U         | 1400mm | 800mm | IP20              | 1                | Black Grey |
| 21630-388     | 33U         | 1600mm | 600mm | IP20              | 1                | Black Grey |

| CatalogNumber | Rack Height | Height | Width | Protection Rating | Package Quantity | Color      |
|---------------|-------------|--------|-------|-------------------|------------------|------------|
| 21630-389     | 33U         | 1600mm | 800mm | IP20              | 1                | Black Grey |
| 21630-390     | 38U         | 1800mm | 600mm | IP20              | 1                | Black Grey |
| 21630-391     | 38U         | 1800mm | 800mm | IP20              | 1                | Black Grey |
| 21630-545     | 24U         | 1200mm | 600mm | IP55              | 1                |            |
| 21630-546     | 24U         | 1200mm | 800mm | IP55              | 1                |            |
| 21630-547     | 29U         | 1400mm | 600mm | IP55              | 1                |            |
| 21630-548     | 29U         | 1400mm | 800mm | IP55              | 1                |            |
| 21630-549     | 33U         | 1600mm | 600mm | IP55              | 1                |            |
| 21630-550     | 33U         | 1600mm | 800mm | IP55              | 1                |            |
| 21630-551     | 38U         | 1800mm | 600mm | IP55              | 1                |            |
| 21630-552     | 38U         | 1800mm | 800mm | IP55              | 1                |            |
| 21630-553     | 42U         | 2000mm | 600mm | IP55              | 1                |            |
| 21630-554     | 42U         | 2000mm | 800mm | IP55              | 1                |            |
| 21630-555     | 47U         | 2200mm | 600mm | IP55              | 1                |            |
| 21630-556     | 47U         | 2200mm | 800mm | IP55              | 1                |            |

Table 2/2

| Catalog Number | Color Code | Finish        | Type       | Works With  |
|----------------|------------|---------------|------------|-------------|
| 21630-122      | RAL 7021   | Powder Coated | Rear Panel | Varistar CP |
| 21630-123      | RAL 7021   | Powder Coated | Rear Panel | Varistar CP |

| Catalog Number | Color Code | Finish        | Type       | Works With  |
|----------------|------------|---------------|------------|-------------|
| 21630-124      | RAL 7021   | Powder Coated | Rear Panel | Varistar CP |
| 21630-125      | RAL 7021   | Powder Coated | Rear Panel | Varistar CP |
| 21630-126      | RAL 7021   | Powder Coated | Rear Panel | Varistar CP |
| 21630-127      | RAL 7021   | Powder Coated | Rear Panel | Varistar CP |
| 21630-198      | RAL 7021   | Powder Coated | Rear Panel | Varistar CP |
| 21630-199      | RAL 7021   | Powder Coated | Rear Panel | Varistar CP |
| 21630-200      | RAL 7021   | Powder Coated | Rear Panel | Varistar CP |
| 21630-201      | RAL 7021   | Powder Coated | Rear Panel | Varistar CP |
| 21630-202      | RAL 7021   | Powder Coated | Rear Panel | Varistar CP |
| 21630-203      | RAL 7021   | Powder Coated | Rear Panel | Varistar CP |
| 21630-204      | RAL 7021   | Powder Coated | Rear Panel | Varistar CP |
| 21630-205      | RAL 7021   | Powder Coated | Rear Panel | Varistar CP |
| 21630-206      | RAL 7021   | Powder Coated | Rear Panel | Varistar CP |
| 21630-207      | RAL 7021   | Powder Coated | Rear Panel | Varistar CP |
| 21630-208      | RAL 7021   | Powder Coated | Rear Panel | Varistar CP |
| 21630-209      | RAL 7021   | Powder Coated | Rear Panel | Varistar CP |
| 21630-384      | RAL 7021   | Powder Coated | Rear Panel | Varistar CP |
| 21630-385      | RAL 7021   | Powder Coated | Rear Panel | Varistar CP |

| Catalog Number | Color Code | Finish        | Type       | Works With  |
|----------------|------------|---------------|------------|-------------|
| 21630-386      | RAL 7021   | Powder Coated | Rear Panel | Varistar CP |
| 21630-387      | RAL 7021   | Powder Coated | Rear Panel | Varistar CP |
| 21630-388      | RAL 7021   | Powder Coated | Rear Panel | Varistar CP |
| 21630-389      | RAL 7021   | Powder Coated | Rear Panel | Varistar CP |
| 21630-390      | RAL 7021   | Powder Coated | Rear Panel | Varistar CP |
| 21630-391      | RAL 7021   | Powder Coated | Rear Panel | Varistar CP |
| 21630-545      |            | Powder Coated | Rear Panel | Varistar CP |
| 21630-546      |            | Powder Coated | Rear Panel | Varistar CP |
| 21630-547      |            | Powder Coated | Rear Panel | Varistar CP |
| 21630-548      |            | Powder Coated | Rear Panel | Varistar CP |
| 21630-549      |            | Powder Coated | Rear Panel | Varistar CP |
| 21630-550      |            | Powder Coated | Rear Panel | Varistar CP |
| 21630-551      |            | Powder Coated | Rear Panel | Varistar CP |
| 21630-552      |            | Powder Coated | Rear Panel | Varistar CP |
| 21630-553      |            | Powder Coated | Rear Panel | Varistar CP |
| 21630-554      |            | Powder Coated | Rear Panel | Varistar CP |
| 21630-555      |            | Powder Coated | Rear Panel | Varistar CP |
| 21630-556      |            | Powder Coated | Rear Panel | Varistar CP |

## ADDITIONAL PRODUCT DETAILS

---

Please purchase the grounding kit separately.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**