

# Varistar CP Flat Top Cover Closed

## Power Utilities

Flat top cover for Varistar CP cabinets without cable entry zones.

### FEATURES

Flat top cover closed

### SPECIFICATIONS

Table 1/2

| Catalog Number | Width  | Depth   | Protection Rating | Color      | Color Code | Finish        |
|----------------|--------|---------|-------------------|------------|------------|---------------|
| 21630-260      | 600 mm | 300 mm  | IP20              | Black Grey | RAL 7021   |               |
| 21630-315      | 600 mm | 300 mm  |                   | Black Grey | RAL 7021   | Powder Coated |
| 21630-557      | 600 mm | 300 mm  | IP55              | Black Grey | RAL 7021   |               |
| 21630-570      | 600 mm | 300 mm  |                   | Black Grey | RAL 7021   | Powder Coated |
| 21630-128      | 600 mm | 1000 mm | IP20              | Black Grey | RAL 7021   |               |
| 21630-129      | 600 mm | 1100 mm | IP20              | Black Grey | RAL 7021   |               |
| 21630-130      | 600 mm | 1200 mm | IP20              | Black Grey | RAL 7021   |               |
| 21630-186      | 600 mm | 600 mm  |                   | Black Grey | RAL 7021   | Powder Coated |
| 21630-187      | 600 mm | 800 mm  |                   | Black Grey | RAL 7021   | Powder Coated |

| CatalogNumber | Width  | Depth   | Protection Rating | Color      | Color Code | Finish        |
|---------------|--------|---------|-------------------|------------|------------|---------------|
| 21630-188     | 600 mm | 900 mm  |                   | Black Grey | RAL 7021   | Powder Coated |
| 21630-189     | 600 mm | 1000 mm |                   | Black Grey | RAL 7021   | Powder Coated |
| 21630-190     | 600 mm | 1100 mm |                   | Black Grey | RAL 7021   | Powder Coated |
| 21630-191     | 600 mm | 1200 mm |                   | Black Grey | RAL 7021   | Powder Coated |
| 21630-254     | 600 mm | 600 mm  | IP20              | Black Grey | RAL 7021   |               |
| 21630-255     | 600 mm | 800 mm  | IP20              | Black Grey | RAL 7021   |               |
| 21630-256     | 600 mm | 900 mm  | IP20              | Black Grey | RAL 7021   |               |
| 21630-558     | 600 mm | 600 mm  | IP55              | Black Grey | RAL 7021   |               |
| 21630-559     | 600 mm | 800 mm  | IP55              | Black Grey | RAL 7021   |               |
| 21630-560     | 600 mm | 900 mm  | IP55              | Black Grey | RAL 7021   |               |
| 21630-561     | 600 mm | 1000 mm | IP55              | Black Grey | RAL 7021   |               |
| 21630-562     | 600 mm | 1100 mm | IP55              | Black Grey | RAL 7021   |               |
| 21630-563     | 600 mm | 1200 mm | IP55              | Black Grey | RAL 7021   |               |
| 21630-571     | 600 mm | 600 mm  |                   | Black Grey | RAL 7021   | Powder Coated |
| 21630-572     | 600 mm | 800 mm  |                   | Black Grey | RAL 7021   | Powder Coated |
| 21630-573     | 600 mm | 900 mm  |                   | Black Grey | RAL 7021   | Powder Coated |
| 21630-574     | 600 mm | 1000 mm |                   | Black Grey | RAL 7021   | Powder Coated |
| 21630-575     | 600 mm | 1100 mm |                   | Black Grey | RAL 7021   | Powder Coated |

| CatalogNumber | Width  | Depth   | Protection Rating | Color      | Color Code | Finish        |
|---------------|--------|---------|-------------------|------------|------------|---------------|
| 21630-576     | 600 mm | 1200 mm |                   | Black Grey | RAL 7021   | Powder Coated |
| 21630-192     | 800 mm | 600 mm  |                   | Black Grey | RAL 7021   | Powder Coated |
| 21630-257     | 800 mm | 600 mm  | IP20              | Black Grey | RAL 7021   |               |
| 21630-564     | 800 mm | 600 mm  | IP55              | Black Grey | RAL 7021   |               |
| 21630-577     | 800 mm | 600 mm  |                   | Black Grey | RAL 7021   | Powder Coated |
| 21630-131     | 800 mm | 1000 mm | IP20              | Black Grey | RAL 7021   |               |
| 21630-132     | 800 mm | 1100 mm | IP20              | Black Grey | RAL 7021   |               |
| 21630-133     | 800 mm | 1200 mm | IP20              | Black Grey | RAL 7021   |               |
| 21630-193     | 800 mm | 800 mm  |                   | Black Grey | RAL 7021   | Powder Coated |
| 21630-194     | 800 mm | 900 mm  |                   | Black Grey | RAL 7021   | Powder Coated |
| 21630-195     | 800 mm | 1000 mm |                   | Black Grey | RAL 7021   | Powder Coated |
| 21630-196     | 800 mm | 1100 mm |                   | Black Grey | RAL 7021   | Powder Coated |
| 21630-197     | 800 mm | 1200 mm |                   | Black Grey | RAL 7021   | Powder Coated |
| 21630-258     | 800 mm | 800 mm  | IP20              | Black Grey | RAL 7021   |               |
| 21630-259     | 800 mm | 900 mm  | IP20              | Black Grey | RAL 7021   |               |
| 21630-565     | 800 mm | 800 mm  | IP55              | Black Grey | RAL 7021   |               |
| 21630-566     | 800 mm | 900 mm  | IP55              | Black Grey | RAL 7021   |               |
| 21630-567     | 800 mm | 1000 mm | IP55              | Black Grey | RAL 7021   |               |

| CatalogNumber | Width  | Depth   | Protection Rating | Color      | Color Code | Finish        |
|---------------|--------|---------|-------------------|------------|------------|---------------|
| 21630-568     | 800 mm | 1100 mm | IP55              | Black Grey | RAL 7021   |               |
| 21630-569     | 800 mm | 1200 mm | IP55              | Black Grey | RAL 7021   |               |
| 21630-578     | 800 mm | 800 mm  |                   | Black Grey | RAL 7021   | Powder Coated |
| 21630-579     | 800 mm | 900 mm  |                   | Black Grey | RAL 7021   | Powder Coated |
| 21630-580     | 800 mm | 1000 mm |                   | Black Grey | RAL 7021   | Powder Coated |
| 21630-581     | 800 mm | 1100 mm |                   | Black Grey | RAL 7021   | Powder Coated |
| 21630-582     | 800 mm | 1200 mm |                   | Black Grey | RAL 7021   | Powder Coated |

| Table 2/2      |          |                        |        |             |
|----------------|----------|------------------------|--------|-------------|
| Catalog Number | Material | Product Type           | Type   | Works With  |
| 21630-260      | Steel    | Cabinet/Rack Top Cover | Closed |             |
| 21630-315      | Steel    | Cabinet/Rack Top Cover | Closed | Varistar CP |
| 21630-557      | Steel    | Cabinet/Rack Top Cover | Closed |             |
| 21630-570      | Steel    | Cabinet/Rack Top Cover | Closed | Varistar CP |
| 21630-128      | Steel    | Cabinet/Rack Top Cover | Closed |             |
| 21630-129      | Steel    | Cabinet/Rack Top Cover | Closed |             |
| 21630-130      | Steel    | Cabinet/Rack Top Cover | Closed |             |
| 21630-186      | Steel    | Cabinet/Rack Top Cover | Closed | Varistar CP |
| 21630-187      | Steel    | Cabinet/Rack Top Cover | Closed | Varistar CP |
| 21630-188      | Steel    | Cabinet/Rack Top Cover | Closed | Varistar CP |

| Catalog Number | Material | Product Type           | Type   | Works With  |
|----------------|----------|------------------------|--------|-------------|
| 21630-189      | Steel    | Cabinet/Rack Top Cover | Closed | Varistar CP |
| 21630-190      | Steel    | Cabinet/Rack Top Cover | Closed | Varistar CP |
| 21630-191      | Steel    | Cabinet/Rack Top Cover | Closed | Varistar CP |
| 21630-254      | Steel    | Cabinet/Rack Top Cover | Closed |             |
| 21630-255      | Steel    | Cabinet/Rack Top Cover | Closed |             |
| 21630-256      | Steel    | Cabinet/Rack Top Cover | Closed |             |
| 21630-558      | Steel    | Cabinet/Rack Top Cover | Closed |             |
| 21630-559      | Steel    | Cabinet/Rack Top Cover | Closed |             |
| 21630-560      | Steel    | Cabinet/Rack Top Cover | Closed |             |
| 21630-561      | Steel    | Cabinet/Rack Top Cover | Closed |             |
| 21630-562      | Steel    | Cabinet/Rack Top Cover | Closed |             |
| 21630-563      | Steel    | Cabinet/Rack Top Cover | Closed |             |
| 21630-571      | Steel    | Cabinet/Rack Top Cover | Closed | Varistar CP |
| 21630-572      | Steel    | Cabinet/Rack Top Cover | Closed | Varistar CP |
| 21630-573      | Steel    | Cabinet/Rack Top Cover | Closed | Varistar CP |
| 21630-574      | Steel    | Cabinet/Rack Top Cover | Closed | Varistar CP |
| 21630-575      | Steel    | Cabinet/Rack Top Cover | Closed | Varistar CP |
| 21630-576      | Steel    | Cabinet/Rack Top Cover | Closed | Varistar CP |

| Catalog Number | Material | Product Type           | Type   | Works With  |
|----------------|----------|------------------------|--------|-------------|
| 21630-192      | Steel    | Cabinet/Rack Top Cover | Closed | Varistar CP |
| 21630-257      | Steel    | Cabinet/Rack Top Cover | Closed |             |
| 21630-564      | Steel    | Cabinet/Rack Top Cover | Closed |             |
| 21630-577      | Steel    | Cabinet/Rack Top Cover | Closed | Varistar CP |
| 21630-131      | Steel    | Cabinet/Rack Top Cover | Closed |             |
| 21630-132      | Steel    | Cabinet/Rack Top Cover | Closed |             |
| 21630-133      | Steel    | Cabinet/Rack Top Cover | Closed |             |
| 21630-193      | Steel    | Cabinet/Rack Top Cover | Closed | Varistar CP |
| 21630-194      | Steel    | Cabinet/Rack Top Cover | Closed | Varistar CP |
| 21630-195      | Steel    | Cabinet/Rack Top Cover | Closed | Varistar CP |
| 21630-196      | Steel    | Cabinet/Rack Top Cover | Closed | Varistar CP |
| 21630-197      | Steel    | Cabinet/Rack Top Cover | Closed | Varistar CP |
| 21630-258      | Steel    | Cabinet/Rack Top Cover | Closed |             |
| 21630-259      | Steel    | Cabinet/Rack Top Cover | Closed |             |
| 21630-565      | Steel    | Cabinet/Rack Top Cover | Closed |             |
| 21630-566      | Steel    | Cabinet/Rack Top Cover | Closed |             |
| 21630-567      | Steel    | Cabinet/Rack Top Cover | Closed |             |
| 21630-568      | Steel    | Cabinet/Rack Top Cover | Closed |             |

| Catalog Number | Material | Product Type           | Type   | Works With  |
|----------------|----------|------------------------|--------|-------------|
| 21630-569      | Steel    | Cabinet/Rack Top Cover | Closed |             |
| 21630-578      | Steel    | Cabinet/Rack Top Cover | Closed | Varistar CP |
| 21630-579      | Steel    | Cabinet/Rack Top Cover | Closed | Varistar CP |
| 21630-580      | Steel    | Cabinet/Rack Top Cover | Closed | Varistar CP |
| 21630-581      | Steel    | Cabinet/Rack Top Cover | Closed | Varistar CP |
| 21630-582      | Steel    | Cabinet/Rack Top Cover | Closed | Varistar CP |

## ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**