

# 19" Equipment Shelf, Depth-Adjustable

Schroff 19" equipment shelf with 10 Kg lead capacity helps rack managers assimilate critical equipment into the cabinet.



## CERTIFICATIONS



## FEATURES

Depth adjustable in 25 mm grid increments, forward protrusion min. 26 mm

Installation height 2 U

Static load-carrying capacity 15 kg

## SPECIFICATIONS

**Product Type:** Shelf

**Material:** Steel

Table 1/2

Catalog Number	Width	Depth	Package Quantity	Color	Color Code	Finish
20118-786	430mm	250mm	1	Black Grey	RAL 7021	Powder Coated
20118-787	430mm	300mm	1	Black Grey	RAL 7021	Powder Coated
20118-788	430mm	400mm	1	Black Grey	RAL 7021	Powder Coated

CatalogNumber	Width	Depth	Package Quantity	Color	Color Code	Finish
20118-789	430mm	250mm	1	Light Grey	RAL 7035	Powder Coated
20118-790	430mm	300mm	1	Light Grey	RAL 7035	Powder Coated
20118-791	430mm	400mm	1	Light Grey	RAL 7035	Powder Coated

Table 2/2

Catalog Number	Type	Quick Ship
20118-786	Equipment Shelf	No
20118-787	Equipment Shelf	No
20118-788	Equipment Shelf	No
20118-789	Equipment Shelf	No
20118-790	Equipment Shelf	No
20118-791	Equipment Shelf	No

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations

+1.763.422.2661

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**