


# Cable to Web of Rail Replacement Mold Pair, Signal



## FEATURES

Replacement mold pair designed for the installation of track circuits and jumper bonds to the neutral axis

Sold in pairs

## SPECIFICATIONS

**Material:** Graphite

Table 1/1

| Catalog Number | Rail Type                       | Bond Terminal Style | Conductor Size              | Conductor Outer Diameter, Nominal | Welder Style | Bond Clips Included |
|----------------|---------------------------------|---------------------|-----------------------------|-----------------------------------|--------------|---------------------|
| SBB200R        | 85 lb to 141 lb T-Rail Sections | 1" Tab              | 10 mm <sup>2</sup> Stranded | 4.12mm                            | TB5, T21     | No                  |
| SBB200A        | 85 lb to 141 lb T-Rail Sections | 3/4" XS             | 3/16" Bondstrand            | 4.76mm                            | TB5, T21     | Yes                 |
| SBB200B        | 85 lb to 141 lb T-Rail Sections | 3/4" Tab            | 3/16" Bondstrand            | 4.76mm                            | TB5, T21     | Yes                 |
| SBB200C        | 85 lb to 141 lb T-Rail Sections | 1" Tab              | 3/16" Bondstrand            | 4.76mm                            | TB5, T21     | Yes                 |
| SBB200C12AS    | 12 lb ASCE                      | 1" Tab              | 3/16" Bondstrand            | 4.76mm                            | T21, TB5     | No                  |

| CatalogNumber | Rail Type                       | Bond Terminal Style | Conductor Size                | Conductor OuterDiameter, Nominal | Welder Style | Bond Clips Included |
|---------------|---------------------------------|---------------------|-------------------------------|----------------------------------|--------------|---------------------|
| SBB200D       | 85 lb to 141 lb T-Rail Sections | 1 1/2" Tab          | 3/16" Bondstrand              | 4.76mm                           | T21, TB5     | No                  |
| SBB200G       | 85 lb to 141 lb T-Rail Sections | 1" Tab              | 3/16" Bondstrand              | 4.76mm                           | T21, TB5     | No                  |
| SBB200U       | RI60                            | 1" Tab              | 3/16" Bondstrand              | 4.76mm                           | TB5, T21     | No                  |
| SBB200Y       | 85 lb to 141 lb T-Rail Sections | 1" Tab              | 16 mm <sup>2</sup> Concentric | 5.18mm                           | T21, TB5     | No                  |
| SBB200L       | 85 lb to 141 lb T-Rail Sections | 1" Tab              | 22 mm <sup>2</sup> Ropelay    | 6.1mm                            | T21, TB5     | No                  |
| SBB200X       | 85 lb to 141 lb T-Rail Sections | 1" Tab              | 25 mm <sup>2</sup> Stranded   | 6.6mm                            | TB5, T21     | No                  |
| SBB200P       | 85 lb to 141 lb T-Rail Sections | 1" Tab              | 35 mm <sup>2</sup> Concentric | 7.75mm                           | T21, TB5     | Not Required        |
| SBB200E       | 85 lb to 141 lb T-Rail Sections | 1" Tab              | 5/16" Bondstrand              | 7.94mm                           | TB5, T21     | Yes                 |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE