

Air-to-Water Heat Exchanger, BLU



Industrial air-to-water heat exchangers remove heat from enclosures by using chilled fluid, which offers a reliable and low maintenance enclosure cooling option.

CERTIFICATIONS



FEATURES

Finish: RAL 7035 for the galvanized steel versions

Internal temperature range: +20 °C to +60 °C

Ambient temperature range: +1 °C to +60 °C | +1 °C to +70 °C

Pack quantity: 1

SPECIFICATIONS

Cable Length: 3m
Rated Frequency: 50 – 60Hz
Material: Galvanized Steel
Protection Rating: IP55

Table 1/1

Catalog Number	Capacity Watts @ Δt 25°C	Nominal Voltage	Height	Width	Depth	Certifications
BLU10BX0B	1000W	230V	453mm	311mm	115mm	CE
BLU10BXUB	1000W	230V	453mm	311mm	115mm	CE
BLU10CX0B	1000W	115V	453mm	311mm	115mm	CE
BLU18BX0B	1750W	230V	901mm	398mm	137mm	CE
BLU18BXUB	1750W	230V	901mm	398mm	137mm	CE, UL Registered US & C
BLU18CX0B	1750W	115V	901mm	398mm	137mm	CE
BLU35BX0B	3500W	230V	1148mm	398mm	163mm	CE
BLU35BXUB	3500W	230V	1148mm	398mm	163mm	CE, UR
BLU35CX0B	3500W	115V	1148mm	398mm	163mm	CE
BLU45BX0B	4500W	230V	1148mm	398mm	163mm	CE
BLU45BXUB	4500W	230V	1148mm	398mm	163mm	CE, UR
BLU45CX0B	4500W	115V	1148mm	398mm	163mm	CE
BLU25BX0B	2500W	230V	901mm	398mm	137mm	CE
BLU25BXUB	2500W	230V	901mm	398mm	137mm	CE, UL Registered US & C
BLU25CX0B	2500W	115V	901mm	398mm	137mm	CE
BLU60GX0B	6000W	400V	1502mm	450mm	163mm	CE

Catalog Number	Capacity Watts @ Δt 25°C	Nominal Voltage	Height	Width	Depth	Certifications
BLU60BX0B	6000W	230V	1502mm	450mm	163mm	CE
BLU60BXUB	6000W	230V	1502mm	450mm	163mm	CE, UR
BLU60CX0B	6000W	115V	1502mm	450mm	163mm	CE
BLUA5GX0B	15000W	400V	1935mm	797mm	206mm	CE
BLUA0BX0B	10000W	230V	1935mm	797mm	206mm	CE
BLUA5BX0B	15000W	230V	1935mm	797mm	206mm	CE
BLUB5BX0B	25000W	230V	1935mm	797mm	350mm	CE
BLUA0GX0B	10000W	400V	1935mm	797mm	206mm	CE
BLUB5KX0B	25000W	400V	1935mm	797mm	350mm	CE

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE