

# Varistar CP Steel Door, Plain, Multi-Point Locking

## Power Utilities

EMC and IP55 Steel Door with lever handle and 4-Point locking.

### FEATURES

Lever handle with push button

Opening angle 180°

Steel door with 4-point locking for EMC applications

### SPECIFICATIONS

Table 1/2

| Catalog Number | Rack Height | Height  | Width  | Color      | Color Code | Locking Type    |
|----------------|-------------|---------|--------|------------|------------|-----------------|
| 21630-521      | 24 U        | 1200 mm | 600 mm | Black Grey | RAL 7021   | 3-Point Locking |
| 21630-522      | 24 U        | 1200 mm | 800 mm | Black Grey | RAL 7021   | 3-Point Locking |
| 21630-523      | 29 U        | 1400 mm | 600 mm | Black Grey | RAL 7021   | 3-Point Locking |
| 21630-524      | 29 U        | 1400 mm | 800 mm | Black Grey | RAL 7021   | 3-Point Locking |
| 21630-525      | 33 U        | 1600 mm | 600 mm | Black Grey | RAL 7021   | 4-Point Locking |
| 21630-526      | 33 U        | 1600 mm | 800 mm | Black Grey | RAL 7021   | 4-Point Locking |
| 21630-527      | 38 U        | 1800 mm | 600 mm | Black Grey | RAL 7021   | 4-Point Locking |
| 21630-528      | 38 U        | 1800 mm | 800 mm | Black Grey | RAL 7021   | 4-Point Locking |

| CatalogNumber | Rack Height | Height  | Width  | Color      | Color Code | Locking Type    |
|---------------|-------------|---------|--------|------------|------------|-----------------|
| 21630-529     | 42 U        | 2000 mm | 600 mm | Black Grey | RAL 7021   | 4-Point Locking |
| 21630-530     | 42 U        | 2000 mm | 800 mm | Black Grey | RAL 7021   | 4-Point Locking |
| 21630-531     | 47 U        | 2200 mm | 600 mm | Black Grey | RAL 7021   | 5-Point Locking |
| 21630-532     | 47 U        | 2200 mm | 800 mm | Black Grey | RAL 7021   | 5-Point Locking |

Table 2/2

| Catalog Number | Product Type | Protection Rating |
|----------------|--------------|-------------------|
| 21630-521      | Cabinet Door | IP55              |
| 21630-522      | Cabinet Door | IP55              |
| 21630-523      | Cabinet Door | IP55              |
| 21630-524      | Cabinet Door | IP55              |
| 21630-525      | Cabinet Door | IP55              |
| 21630-526      | Cabinet Door | IP55              |
| 21630-527      | Cabinet Door | IP55              |
| 21630-528      | Cabinet Door | IP55              |
| 21630-529      | Cabinet Door | IP55              |
| 21630-530      | Cabinet Door | IP55              |
| 21630-531      | Cabinet Door | IP55              |
| 21630-532      | Cabinet Door | IP55              |

## ADDITIONAL PRODUCT DETAILS

---

Please purchase the grounding kit separately.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**