

# Varistar CP Seismic Base/Plinth



A plinth allows functional storage of excess cable assemblies and protects the bottom part of the cabinet against rodents.

## FEATURES

2 support profiles, St, 10 mm, side

Seismic dynamic load-carrying capacity 500 kg

Height 103 mm

2 covers, St, 10 mm, front and rear

Conforms to NEBS, Earthquake secure (up) to Bellcore Zone 4, tested with 500 KGs, Mounting holes for fitting of base

Access possible from front and rear

## SPECIFICATIONS

**Static Load:** 400kg

**Product Type:** Cabinet/Rack Base

**Material:** Steel

Table 1/2

| Catalog Number | Width | Depth  | Package Quantity | Color      | Color Code | Complies With            |
|----------------|-------|--------|------------------|------------|------------|--------------------------|
| 21630-110      | 600mm | 600mm  | 1                | Black Grey | RAL 7021   | IEC 61587-1, IEC 61587-2 |
| 21630-111      | 600mm | 800mm  | 1                | Black Grey | RAL 7021   | IEC 61587-1, IEC 61587-2 |
| 21630-112      | 600mm | 1000mm | 1                | Black Grey | RAL 7021   | IEC 61587-1, IEC 61587-2 |

| CatalogNumber | Width | Depth  | Package Quantity | Color      | Color Code | Complies With               |
|---------------|-------|--------|------------------|------------|------------|-----------------------------|
| 21630-113     | 600mm | 1200mm | 1                | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2 |
| 21630-114     | 800mm | 600mm  | 1                | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2 |
| 21630-115     | 800mm | 800mm  | 1                | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2 |
| 21630-116     | 800mm | 1000mm | 1                | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2 |
| 21630-117     | 800mm | 1200mm | 1                | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2 |

Table 2/2

| Catalog Number | Finish        | Height | Type        | Works With  | Quick Ship |
|----------------|---------------|--------|-------------|-------------|------------|
| 21630-110      | Powder Coated | 103mm  | Base Plinth | Varistar CP | No         |
| 21630-111      | Powder Coated | 103mm  | Base Plinth | Varistar CP | No         |
| 21630-112      | Powder Coated | 103mm  | Base Plinth | Varistar CP | No         |
| 21630-113      | Powder Coated | 103mm  | Base Plinth | Varistar CP | No         |
| 21630-114      | Powder Coated | 103mm  | Base Plinth | Varistar CP | No         |
| 21630-115      | Powder Coated | 103mm  | Base Plinth | Varistar CP | No         |
| 21630-116      | Powder Coated | 800mm  | Base Plinth | Varistar CP | No         |
| 21630-117      | Powder Coated | 103mm  | Base Plinth | Varistar CP | No         |

## ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause

product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

**Europe**

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

**Asia**

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

**Middle East & India**

Dubai, United Arab  
Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**