

# Guide Rail With DIN Connector Fixing

## Power Utilities



The the standard type guide rail with connector fixing allows the user to clip the DIN connectors directly onto the guide rails. Only applicable with Euroboards with the dimensions 100 x 160 mm and 100 x 220 mm. Suitable for RatiopacPRO/-AIR, PropacPRO, CompacPRO and EuropacPRO.

## CERTIFICATIONS



## FEATURES

Easy and economic mounting of connectors through snap connections as alternative to z-rails or horizontal rails with integrated z-rail

For single Euroboard format 100 × 160 mm or 100 × 220 mm; not suitable for double Euroboard format

Plastic guide rail, one piece, red, for 2 mm groove width

Can be clipped into horizontal rails in Al extrusion

Can be clipped into 1.5 mm thick plate

Storage temperature: from -40 °C ... 130 °C

## SPECIFICATIONS

Table 1/2

| Catalog Number | Package Quantity | Board Depth | Groove Width | Color | Material | Product Family |
|----------------|------------------|-------------|--------------|-------|----------|----------------|
|----------------|------------------|-------------|--------------|-------|----------|----------------|

|           |   |        |   |     |         |                                                                                                         |
|-----------|---|--------|---|-----|---------|---------------------------------------------------------------------------------------------------------|
| 64560-075 | 1 | 220 mm | 2 | Red | Plastic | EuropacPRO,<br>RatiopacPRO,<br>RatiopacPRO<br>AIR,<br>CompacPRO,<br>PropacPRO,<br>MultipacPRO,<br>Inpac |
| 64560-074 | 1 | 160 mm | 2 | Red | Plastic | EuropacPRO,<br>RatiopacPRO,<br>RatiopacPRO<br>AIR,<br>CompacPRO,<br>PropacPRO,<br>MultipacPRO,<br>Inpac |

Table 2/2

| Catalog Number | Product Type | Type                        | Works With               | Package Unit |
|----------------|--------------|-----------------------------|--------------------------|--------------|
| 64560-075      | Guide Rail   | Standard with DIN Connector | Subracks, Cases, Chassis | Pair         |
| 64560-074      | Guide Rail   | Standard with DIN Connector | Subracks, Cases, Chassis | Pair         |

## ADDITIONAL PRODUCT DETAILS

Delivery is in standard pack multiples. Pricing is per individual item.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**