

# 19" Cable Ducting and Cable Through Ducting

## Data Solutions

Cable ducting apparatus for smart cable management.



### CERTIFICATIONS



### FEATURES

Cable ducting apparatus for smart cable management

### SPECIFICATIONS

**Accessory Type:** Front panel  
**Product Type:** Front Panel  
**Material:** Steel

Table 1/3

| Catalog Number | Rack Height | Mounting       | Package Quantity | Front Finish | Rear Finish | Color Code |
|----------------|-------------|----------------|------------------|--------------|-------------|------------|
| 20118-757      | 1U          | Screw-on Front | 1                | Painted      | Painted     | RAL 7035   |
| 20118-758      | 1U          | Screw-on Front | 1                | Painted      | Painted     | RAL 7021   |

| CatalogNumber | Rack Height | Mounting       | Package Quantity | Front Finish | Rear Finish | Color Code |
|---------------|-------------|----------------|------------------|--------------|-------------|------------|
| 20118-759     | 2U          | Screw-on Front | 1                | Painted      | Painted     | RAL 7035   |
| 20118-760     | 2U          | Screw-on Front | 1                | Painted      | Painted     | RAL 7021   |

Table 2/3

| Catalog Number | Depth | EMC Shielding | Finish        | Height | Rack Width | Type            |
|----------------|-------|---------------|---------------|--------|------------|-----------------|
| 20118-757      | 1.5mm | No            | Powder Coated | 42.6mm | 95HP       | 19" Front Panel |
| 20118-758      | 1.5mm | No            | Powder Coated | 42.6mm | 95HP       | 19" Front Panel |
| 20118-759      | 1.5mm | No            | Powder Coated | 81.7mm | 95HP       | 19" Front Panel |
| 20118-760      | 1.5mm | No            | Powder Coated | 81.7mm | 95HP       | 19" Front Panel |

Table 3/3

| Catalog Number | Width |
|----------------|-------|
| 20118-757      | 483mm |
| 20118-758      | 483mm |
| 20118-759      | 483mm |
| 20118-760      | 483mm |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**