


# EuropacPRO Guide Rails to Accomodate Conduction Cooled Assemblies



The adapter is the interface between a subrack and the conduction cooled assemblies (CCAs).

## CERTIFICATIONS



## FEATURES

Adapter to hold conduction cooled assemblies (CCAs) in subracks

## SPECIFICATIONS

|                        |                                                                |
|------------------------|----------------------------------------------------------------|
| <b>Material:</b>       | Aluminum                                                       |
| <b>Works With:</b>     | Subracks; Cases                                                |
| <b>Product Family:</b> | EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO |
| <b>Product Type:</b>   | Guide Rail                                                     |

Table 1/2

| Catalog Number | Type                           | Package Quantity | Groove Width | Finish     | Length | Package Unit |
|----------------|--------------------------------|------------------|--------------|------------|--------|--------------|
| 24566-004      | Conduction Cooled Assembly VPX | 2                | 13.3         | Passivated | 160mm  | Pair         |

| CatalogNumber | Type                                  | Package Quantity | Groove Width | Finish     | Length | Package Unit |
|---------------|---------------------------------------|------------------|--------------|------------|--------|--------------|
| 24566-005     | Conduction Cooled Assembly CompactPCI | 2                | 13.3         | Passivated | 160mm  | Pair         |

Table 2/2

| Catalog Number | Quick Ship |
|----------------|------------|
| 24566-004      | No         |
| 24566-005      | No         |

## ADDITIONAL PRODUCT DETAILS

Suitable for heavy and rugged horizontal rails.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**