

SBS-R Control Panel for Hot Water Temperature Maintenance



SPECIFICATIONS

Phase Quantity:	3
IP Rating:	IP55
Protection:	Miniature- / Earth Leakage Circuit Breaker
Mounting:	Wall Mounted
Over Voltage Protection:	Yes

Table 1/2						
Catalog Number	Item Name	Group Quantity	Circuit Breaker Quantity	Circuit Breaker	Main Switch Current Rating	Circuit Breaker Quantity, 30 mA
1244-016639	SBS-R-HWAT-1X20A	1	1	20 A, Type C	40	1
1244-016640	SBS-R-HWAT-3X20A	1	3	20 A, Type C	40	1
1244-021423	SBS-R-HWAT-1X13A	1	1	13 A, Type C	40	1
1244-021424	SBS-R-HWAT-1X16A	1	1	16 A, Type C	40	1
1244-021425	SBS-R-HWAT-3X16A	1	3	16 A, Type C	40	1
1244-021426	SBS-R-HWAT-6X16A	2	1	16 A, Type C	40	2

Table 2/2

Catalog Number	Item Name	Height	Width	Depth	Housing Material
1244-016639	SBS-R-HWAT-1X20A	400	300	210	Metal
1244-016640	SBS-R-HWAT-3X20A	600	400	210	Metal
1244-021423	SBS-R-HWAT-1X13A	400	300	210	Metal
1244-021424	SBS-R-HWAT-1X16A	400	300	210	Metal
1244-021425	SBS-R-HWAT-3X16A	600	400	210	Metal
1244-021426	SBS-R-HWAT-6X16A	600	600	210	Metal

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258
 Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
 Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
 Fax +86.21.5426.3167
cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800
 Fax +1.713.868.2333
thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT