


# Water Pipe Ground Clamp



The nVent ERICO Water Pipe Ground Clamp provides a highly reliable method for grounding copper conductors to metallic water pipes or ground rods, essential for electrical safety in residential, commercial, and industrial systems. Constructed from high-strength silicone bronze, this clamp ensures excellent durability, corrosion resistance, and secure, long-lasting electrical connections. Its robust design makes it a trusted component for creating effective grounding paths in accordance with applicable electrical codes and standards.

## CERTIFICATIONS



## FEATURES

Manufactured from high-strength silicone bronze for superior durability and corrosion resistance

Used for connecting copper conductors to metallic water pipe or ground rods

Designed for effectively connecting copper conductors to metallic water pipes or ground rods

Ensures a secure and low-resistance path for grounding applications

Suitable for a range of conductor and pipe sizes

## SPECIFICATIONS


**Material:** Silicon Bronze

Table 1/1

| Catalog Number | Article Number | Pipe Size, Nominal (Ø) | Pipe Size, Actual (Ø) | Certifications |
|----------------|----------------|------------------------|-----------------------|----------------|
| CWP1JJ         | 710262         | 1/2" - 1"              | 12.7 - 25.4 mm        |                |
| CWP1JU         | 710266         | 1/2" - 1"              | 12.7 - 25.4 mm        | cUL, UL, CSA   |

| Catalog Number | Article Number | Pipe Size, Nominal (Ø) | Pipe Size, Actual (Ø) | Certifications |
|----------------|----------------|------------------------|-----------------------|----------------|
| CWP4J          | 710264         | 2 1/2" - 4"            | 63.5 - 101.6 mm       | CSA, cUL, UL   |

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**⚠ WARNING:** This product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov).

### North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

### Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

### Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

### APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**