


Front Panel EMC Textile Shielding Kit, -40 up to +85°C

Power Utilities



The textile EMC gaskets are inserted into a slot on the right hand side of the U-shaped front panels. The gaskets are glued to the front panel. For an expanded temperature range up to +85°C.

CERTIFICATIONS



FEATURES

Textile EMC gasket is affixed laterally on the front panel or in the groove of the right-hand profile as appropriate.

Profile seal is bonded onto the contact surface of the 19" bracket or of the rear angle and sets up the conductive connection to the U-shaped front panels

Temperature range -40 °C ... +85 °C

SPECIFICATIONS

Table 1/1

Catalog Number	Rack Height	Package Quantity	Product Family	Product Type	Works With
----------------	-------------	------------------	----------------	--------------	------------

21102-857	2 U	10	EuropacPRO, PropacPRO, RatiopacPRO AIR, PropacPRO, Frame Type Plug-In Unit	Shielding Kit	Subracks, Cases, Front Panels
21102-853	3 U	10	EuropacPRO, PropacPRO, RatiopacPRO AIR, PropacPRO, Frame Type Plug-In Unit	Shielding Kit	Subracks, Cases, Front Panels
21102-854	3 U	100	EuropacPRO, PropacPRO, RatiopacPRO AIR, PropacPRO, Frame Type Plug-In Unit	Shielding Kit	Subracks, Cases, Front Panels
21102-858	4 U	10	EuropacPRO, PropacPRO, RatiopacPRO AIR, PropacPRO, Frame Type Plug-In Unit	Shielding Kit	Subracks, Cases, Front Panels
21102-978	5 U	10	EuropacPRO, PropacPRO, RatiopacPRO AIR, PropacPRO, Frame Type Plug-In Unit	Shielding Kit	Subracks, Cases, Front Panels
21102-855	6 U	10	EuropacPRO, PropacPRO, RatiopacPRO AIR, PropacPRO, Frame Type Plug-In Unit	Shielding Kit	Subracks, Cases, Front Panels
21102-856	6 U	100	EuropacPRO, PropacPRO, RatiopacPRO AIR, PropacPRO, Frame Type Plug-In Unit	Shielding Kit	Subracks, Cases, Front Panels
21102-859	9 U	10	EuropacPRO, PropacPRO, RatiopacPRO AIR, PropacPRO, Frame Type Plug-In Unit	Shielding Kit	Subracks, Cases, Front Panels

ADDITIONAL PRODUCT DETAILS

EMC gaskets (textile) are required for shielding the front panels.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE