


Horizontal Rail, Rear, Type R-VT, Rugged, 1000 mm

CATALOG NUMBER

34566-701



Combinations of horizontal rails and side panels

		"R" can be combined				"V" combination not recommended			
Horizontal rail	Rugged R	-	+	+	+	+	+	+	+
	Rugged V	+	+	+	+	+	+	+	+
	Rugged T	+	+	+	+	+	+	+	+
	Rugged L	+	+	+	+	+	+	+	+
Side panel	Light L	-	-	-	-	-	-	-	-
	Frontier L	-	-	-	-	-	-	-	-
	Heavy L	-	-	-	-	-	-	-	-
	Rugged L	-	-	-	-	-	-	-	-

Legend: "+" can be combined, "-" combination not recommended

The horizontal rail, type rugged VT enables the direct assembly of a backplane.

CERTIFICATIONS



FEATURES

Type R-VT "rugged" horizontal rail with 3-hole fixing for increased robustness

Aluminum extrusion, anodized finish, conductive contact surface

PRODUCT ATTRIBUTES

Rack Width: 195HP

Package Quantity: 1

Finish: Anodized

Length: 1000mm

Material: Aluminum

Product Family: EuropacPRO

Product Type: Horizontal Rail

ADDITIONAL PRODUCT DETAILS

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE