

# CleanTray 90-Degree Elbow



Clean Tray 90-Degree Elbows are used for right-angle installations. The Clean Tray stainless steel system is designed to protect rated cabling in applications that require frequent washdown.

## FEATURES

---

Clean Tray 90-Degree Elbows are used for right-angle installations

The Clean Tray stainless steel system is designed to protect rated cabling in applications that require frequent washdown

## SPECIFICATIONS

**Finish:** Brushed #3  
**Material:** Stainless Steel 304

Table 1/1

Catalog Number	Type	Height	Width	Thickness	Quick Ship
CT22EFC90SS	Elbow	51mm	51mm	1.27mm	No
CT22EFCNT90SS	Elbow	51mm	51mm	1.27mm	No
CT22EIC90SS	Elbow	51mm	51mm	1.27mm	No
CT22EOC90SS	Elbow	51mm	51mm	1.27mm	No
CT22PEFC90SS	Elbow	51mm	51mm	1.27mm	No
CT33EFC90SS	Elbow	76mm	76mm	1.27mm	No
CT33EIC90SS	Elbow	76mm	76mm	1.27mm	No
CT33EOC90SS	Elbow	76mm	76mm	1.27mm	No
CT44EFC90SS	Elbow	102mm	102mm	1.27mm	No
CT44EFCNT90SS	Elbow	102mm	102mm	1.27mm	No
CT44EIC90SS	Elbow	102mm	102mm	1.27mm	No
CT44EOC90SS	Elbow	102mm	102mm	1.27mm	No
CT44PEFC90SS	Elbow	102mm	102mm	1.27mm	No
CT46EFC90SS	Elbow	102mm	152mm	1.27mm	No
CT46EIC90SS	Elbow	102mm	152mm	1.27mm	No
CT46EOC90SS	Elbow	102mm	152mm	1.27mm	No
CT66EFC90SS	Elbow	152mm	152mm	1.27mm	No

Catalog Number	Type	Height	Width	Thickness	Quick Ship
CT66EFCNT90SS	Elbow	152mm	152mm	1.27mm	No
CT66EIC90SS	Elbow	152mm	152mm	1.27mm	No
CT66EOC90SS	Elbow	152mm	152mm	1.27mm	No
CTS33EFC90SS	Elbow	76mm	76mm	1.27mm	No
CTS33PEFC90SS	Elbow	76mm	76mm	1.27mm	No
CTS44EFC90SS	Elbow	102mm	102mm	1.27mm	No
CTS44PEFC90SS	Elbow	102mm	102mm	1.27mm	No
CTS46EFC90SS	Elbow	102mm	152mm	1.27mm	No
CTS46PEFC90SS	Elbow	102mm	152mm	1.27mm	No
CTS66EFC90SS	Elbow	152mm	152mm	1.27mm	No
CTS66PEFC90SS	Elbow	152mm	152mm	1.27mm	No
CT33EFCNT90SS	Elbow	76mm	76mm	1.27mm	No
CT33PEFC90SS	Elbow	76mm	76mm	1.27mm	No
CT46EFCNT90SS	Elbow	102mm	152mm	1.27mm	No
CT46PEFC90SS	Elbow	102mm	152mm	1.27mm	No
CT66PEFC90SS	Elbow	152mm	152mm	1.27mm	No

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**