


PropacPRO Desktop Case, Unshielded, 2 U, 42 HP, 266 mm

CATALOG NUMBER

14576-021



The nVent SCHROFF PropacPRO case provides electronics protection for 19" and individual electronic assemblies. The aluminum die cast frames and profile sidepanels guarantee a robust solution. In addition an extensive accessory range is available.

CERTIFICATIONS



FEATURES

Desktop case for individual assembly

Ventilation slots in base plate

Retrofitable EMC shielding

Prepared for GND/earthing

Conforms with DIN EN 62368-1

PRODUCT ATTRIBUTES

Rack Height: 2U
Rack Width: 42HP
Depth: 266mm
Package Quantity: 1
Usable Height: 85.1mm
Usable Width: 219mm
Front Frame Construction: Single Piece
Cooling Option: No
Complies With: IEC 60297-3-101
EMC Shielding: No (Retrofittable)
Finish: Passivated; Powder Coated
Height: 111mm
Material: Aluminum
Product Family: PropacPRO
Product Type: Case
Protection Rating: IP20
Static Load: 25kg
Type: Case for Individual Electronic Components
Width: 257mm
Net Weight: 1.66kg

ADDITIONAL PRODUCT DETAILS

Case, 2 U with side panel for tip-up carrying handle on request.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE