

## Rain Hood, ARF



A mild steel rain hood provides shelter via a sloped roof and protects installed components from accumulated water dripping into the enclosure when the door is opened.

### FEATURES

---

Description: To be fitted as an outdoor shelter on single mounted enclosures. The roof is slightly sloped and has a dripstrip. Machining is required. It increases the enclosure dimension in H:60 mm, D:20 mm and W:20 mm.

Material: 1.5 mm mild steel.

Finish: RAL 7035 structured powder coating.

Pack quantity: 1 rain hood with mounting accessories.

Additional information: For exposure to high levels of UV radiation, the ARF should be ordered with 100% polyester paint coating. An additional corrosion protection primer coating is recommended for humid environments. Resistance to corrosion must be taken into consideration for outdoor and indoor applications. The ARF is not compatible with 180° MMH hinges.

SPECIFICATIONS

**Thickness:** 1.5mm  
**Color:** Light Gray  
**Material:** Mild Steel  
**Finish:** Powder Coated  
**Color Code:** RAL 7035

| Table 1/1      |                |        |       |       |                    |                |
|----------------|----------------|--------|-------|-------|--------------------|----------------|
| Catalog Number | Article Number | Height | Width | Depth | Enclosure Material | Product Family |
| ARF02515R5     | ARF02515R5     | 55mm   | 250mm | 155mm | Mild Steel         | Wall Mounted   |
| ARF02521R5     | ARF02521R5     | 60mm   | 250mm | 210mm | Mild Steel         | Wall Mounted   |
| ARF03015R5     | ARF03015R5     | 55mm   | 300mm | 155mm | Mild Steel         | Wall Mounted   |
| ARF03021R5     | ARF03021R5     | 60mm   | 300mm | 210mm | Mild Steel         | Wall Mounted   |
| ARF04015R5     | ARF04015R5     | 55mm   | 400mm | 155mm | Mild Steel         | Wall Mounted   |
| ARF04021R5     | ARF04021R5     | 60mm   | 400mm | 210mm | Mild Steel         | Wall Mounted   |
| ARF04026R5     | ARF04026R5     | 65mm   | 400mm | 260mm | Mild Steel         | Wall Mounted   |
| ARF04030R5     | ARF04030R5     | 68mm   | 400mm | 300mm | Mild Steel         | Wall Mounted   |
| ARF05015R5     | ARF05015R5     | 55mm   | 500mm | 155mm | Mild Steel         | Wall Mounted   |
| ARF05021R5     | ARF05021R5     | 60mm   | 500mm | 210mm | Mild Steel         | Wall Mounted   |
| ARF05026R5     | ARF05026R5     | 65mm   | 500mm | 260mm | Mild Steel         | Wall Mounted   |
| ARF05030R5     | ARF05030R5     | 68mm   | 500mm | 300mm | Mild Steel         | Wall Mounted   |
| ARF06021R5     | ARF06021R5     | 60mm   | 600mm | 210mm | Mild Steel         | Wall Mounted   |
| ARF06026R5     | ARF06026R5     | 65mm   | 600mm | 260mm | Mild Steel         | Wall Mounted   |
| ARF06030R5     | ARF06030R5     | 68mm   | 600mm | 300mm | Mild Steel         | Wall Mounted   |
| ARF06040R5     | ARF06040R5     | 77mm   | 600mm | 400mm | Mild Steel         | Wall Mounted   |

| Catalog Number | Article Number | Height | Width  | Depth | EnclosureMaterial | Product Family |
|----------------|----------------|--------|--------|-------|-------------------|----------------|
| ARF08021R5     | ARF08021R5     | 60mm   | 800mm  | 210mm | Mild Steel        | Wall Mounted   |
| ARF08026R5     | ARF08026R5     | 65mm   | 800mm  | 260mm | Mild Steel        | Wall Mounted   |
| ARF08030R5     | ARF08030R5     | 68mm   | 800mm  | 300mm | Mild Steel        | Wall Mounted   |
| ARF08040R5     | ARF08040R5     | 77mm   | 800mm  | 400mm | Mild Steel        | Wall Mounted   |
| ARF10030R5     | ARF10030R5     | 68mm   | 1000mm | 300mm | Mild Steel        | Wall Mounted   |
| ARF12030R5     | ARF12030R5     | 68mm   | 1200mm | 300mm | Mild Steel        | Wall Mounted   |

## ADDITIONAL PRODUCT DETAILS

Not suitable for AFS.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**