


# SIM STAINLESS STEEL MAST



## FEATURES

Designed to mount Early Streamer Emitter air terminals


Mounts conventional air terminals with appropriate adaptor

## SPECIFICATIONS

Catalog Number	Material	Product	Thread Size(TS)	Length(L)	Thickness(T)	Outer Diameter(O D)	Hardware Included	Unit Weight
SIM28A2	Stainless Steel 304L (EN 1.4306)	Upper Mast Section	M25	2,000 mm	2 mm	28 mm	No	2.300 kg
SIM28A2316	Stainless Steel 316L (EN 1.4404)	Upper Mast Section	M25	2,000 mm	2 mm	28 mm	No	2.300 kg
SIM33B2	Stainless Steel 304L (EN 1.4306)	Mid Mast Section		2,000 mm	2.50 mm	33 mm	Yes	3.500 kg
SIM33B2316	Stainless Steel 316L (EN 1.4404)	Mid Mast Section		2,000 mm	2.50 mm	33 mm	Yes	3.500 kg
SIM33B3	Stainless Steel 304L (EN 1.4306)	Mid Mast Section		3,000 mm	2.50 mm	33 mm	Yes	5.300 kg
SIM33B3316	Stainless Steel 316L (EN 1.4404)	Mid Mast Section		3,000 mm	2.50 mm	33 mm	Yes	5.300 kg
SIM40C2	Stainless Steel 304L (EN 1.4306)	Lower Mast Section		2,000 mm	2.50 mm	40 mm	Yes	4 kg

Catalog Number	Material	Product	Thread Size(TS)	Length(L)	Thickness(T)	Outer Diameter(OD)	Hardware Included	Unit Weight
SIM40C3	Stainless Steel 304L (EN 1.4306)	Lower Mast Section		3,000 mm	2.50 mm	40 mm	Yes	6.050 kg
SIM40C2316	Stainless Steel 316L (EN 1.4404)	Lower Mast Section		2,000 mm	3.55 mm	42.4 mm	Yes	6.930 kg
SIM40C3316	Stainless Steel 316L (EN 1.4404)	Lower Mast Section		3,000 mm	3.55 mm	42.4 mm	Yes	10.400 kg

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical Support

### Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

### Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

### APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:  
nVent.com **CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**