


RatiopacPRO 19" Bracket Kit, Retrofitting



For conversion of Ratiopac cases with cover strip or front handle. The retrofitting of the brackets can be done without disassembly of the case.

CERTIFICATIONS



FEATURES

For conversion of cases with cover strip or front handle

SPECIFICATIONS

Material: Aluminum
Product Type: Bracket
Color Code: RAL 7016

Table 1/2

Catalog Number	Rack Height	Package Quantity	Color	Finish	Product Family	Works With
----------------	-------------	------------------	-------	--------	----------------	------------

24571-994	2U	2	Light Grey	Powder Coated	RatiopacPRO, RatiopacPRO AIR, PropacPRO, CompacPRO	Cases, RatiopacPRO
24571-295	3U	2	Light Grey	Powder Coated	RatiopacPRO, RatiopacPRO AIR, PropacPRO, CompacPRO	Cases, RatiopacPRO
24571-296	4U	2	Light Grey	Powder Coated	RatiopacPRO, RatiopacPRO AIR, PropacPRO, CompacPRO	Cases, RatiopacPRO
24571-298	4U	2	Light Grey	Powder Coated	RatiopacPRO AIR	Cases, RatiopacPRO AIR
24571-992	5U	2	Light Grey	Powder Coated	RatiopacPRO, RatiopacPRO AIR, PropacPRO, CompacPRO	Cases, RatiopacPRO
24571-299	5U	2	Light Grey	Powder Coated	RatiopacPRO AIR	Cases, RatiopacPRO AIR
24571-297	6U	2	Light Grey	Powder Coated	RatiopacPRO, RatiopacPRO AIR, PropacPRO, CompacPRO	Cases, RatiopacPRO
24571-300	7U	2	Light Grey	Powder Coated	RatiopacPRO AIR	Cases, RatiopacPRO AIR

Table 2/2

Catalog Number	Quick Ship
24571-994	No
24571-295	No
24571-296	No
24571-298	No

Catalog Number	Quick Ship
24571-992	No
24571-299	No
24571-297	No
24571-300	No

ADDITIONAL PRODUCT DETAILS

No slide rails may be used when fitting into cabinets or 19" cases.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE