


# Socket Strip, IEC C13



Modular, compact PDU with many function elements. Using a 1 U by 1 U aluminum chassis the PDU can easily be integrated in a rack with IEC C13 outlets.

## CERTIFICATIONS



## FEATURES

230 V, 10 A

Horizontal and vertical mounting

Socket strips can be rotated through all four directions (in 90° increments) during installation

Socket strips with IEC 60320-C13 sockets

Connecting cable 2 m, open end with ferrules

In accordance with IEC 60320

Mounting height 1 U

## SPECIFICATIONS

**Material:** Aluminum; Polyamide

**Color:** Grey

**Product Type:** Socket Strip

Table 1/2

Catalog Number	Socket Type	Socket Quantity	Switched Outlets	Voltage AC	Package Quantity	Depth
----------------	-------------	-----------------	------------------	------------	------------------	-------

60110-290	IEC C13	8	No	230V	1	44mm
60110-291	IEC C13	12	No	230V	1	44mm
60110-292	IEC C13	16	No	230V	1	44mm

Table 2/2			
Catalog Number	Finish	Length	Quick Ship
60110-290	Anodized	438.5mm	No
60110-291	Anodized	438.5mm	No
60110-292	Anodized	608.5mm	No

## ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**