

# Internal Side Panels For Power Distribution, MSPS



The galvanised steel internal side panels, MSPS, segregate vertical sections and allow for mounting of busbar supports, MSHS, as well as other accessories. It is a flexible solution both for fix and plug in systems and allows for meeting form 4 segregation according to IEC 61439.

## FEATURES

Description: Internal side panels to build up sections as from the enclosure frame. Frame hole pattern is needed in front, rear, top and bottom.

Material: 1.5 mm galvanized steel.

Delivery: 1 piece with mounting material.

The side panels segregate vertical sections, allowing customer's to mount main busbar supports (MSHS) and other accessories

A flexible solution for both fix and plug-in systems

The side panels allow customers to build up power distribution configurations to meet form 4 segregation according to IEC 61439

Hole patterns are required in the top, bottom, front and rear of the enclosure, in order to mount the internal side panels

## SPECIFICATIONS

**Thickness:** 1.5mm  
**Finish:** Galvanized  
**Material:** Steel

Table 1/1

| Catalog Number | Height | Width  | Depth | Panel Size   | Enclosure Material | Product Family |
|----------------|--------|--------|-------|--------------|--------------------|----------------|
| MSPS1803       | 1800mm | 88.5mm | 300mm | 1800 x 337mm | Mild Steel         | Free-Standing  |
| MSPS1805       | 1800mm | 88.5mm | 500mm | 1800 x 337mm | Mild Steel         | Free-Standing  |
| MSPS1806       | 1800mm | 26mm   | 600mm | 1800 x 507mm | Mild Steel         | Free-Standing  |
| MSPS1806F      | 1800mm | 26mm   | 600mm | 1800 x 507mm | Mild Steel         | Free-Standing  |
| MSPS1808       | 1800mm | 26mm   | 800mm | 1800 x 507mm | Mild Steel         | Free-Standing  |
| MSPS1808F      | 1800mm | 26mm   | 800mm | 1800 x 507mm | Mild Steel         | Free-Standing  |
| MSPS2003       | 2000mm | 88.5mm | 300mm | 2000 x 337mm | Mild Steel         | Free-Standing  |
| MSPS2005       | 2000mm | 88.5mm | 500mm | 2000 x 337mm | Mild Steel         | Free-Standing  |
| MSPS2006       | 2000mm | 26mm   | 600mm | 2000 x 507mm | Mild Steel         | Free-Standing  |
| MSPS2006F      | 2000mm | 26mm   | 600mm | 2000 x 507mm | Mild Steel         | Free-Standing  |
| MSPS2008       | 2200mm | 26mm   | 800mm | 2200 x 507mm | Mild Steel         | Free-Standing  |
| MSPS2008F      | 2000mm | 26mm   | 800mm | 2000 x 507mm | Mild Steel         | Free-Standing  |
| MSPS2203       | 2200mm | 88.5mm | 300mm | 2200 x 337mm | Mild Steel         | Free-Standing  |
| MSPS2205       | 2200mm | 88.5mm | 500mm | 2200 x 337mm | Mild Steel         | Free-Standing  |
| MSPS2206       | 2200mm | 26mm   | 600mm | 2200 x 507mm | Mild Steel         | Free-Standing  |
| MSPS2206F      | 2200mm | 26mm   | 600mm | 2200 x 507mm | Mild Steel         | Free-Standing  |

| Catalog Number | Height | Width | Depth | Panel Size   | EnclosureMaterial | Product Family |
|----------------|--------|-------|-------|--------------|-------------------|----------------|
| MSPS2208       | 2200mm | 26mm  | 800mm | 2200 x 507mm | Mild Steel        | Free-Standing  |
| MSPS2208F      | 2200mm | 26mm  | 800mm | 2200 x 507mm | Mild Steel        | Free-Standing  |

**WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE