

Novastar Steel Door

Power Utilities



CERTIFICATIONS



FEATURES

St, 1.5 mm

Opening angle 180°, incl. grounding

Can be assembled at front and rear

Lock (2233x) with key

SPECIFICATIONS

Table 1/2

Catalog Number	Color	Color Code	Height	Product Type	Rack Height	Type
25230-020	Black Grey	RAL 7021	323 mm	Cabinet Door	6 U	Steel Door
26230-020	Light Grey	RAL 7035	323 mm	Cabinet Door	6 U	Steel Door
25230-021	Black Grey	RAL 7021	422 mm	Cabinet Door	9 U	Steel Door
26230-021	Light Grey	RAL 7035	422 mm	Cabinet Door	9 U	Steel Door
25230-022	Black Grey	RAL 7021	555 mm	Cabinet Door	12 U	Steel Door
26230-022	Light Grey	RAL 7035	555 mm	Cabinet Door	12 U	Steel Door
25230-023	Black Grey	RAL 7021	733 mm	Cabinet Door	16 U	Steel Door
26230-023	Light Grey	RAL 7035	733 mm	Cabinet Door	16 U	Steel Door
25230-024	Black Grey	RAL 7021	911 mm	Cabinet Door	20 U	Steel Door
26230-024	Light Grey	RAL 7035	911 mm	Cabinet Door	20 U	Steel Door
25230-025	Black Grey	RAL 7021	1133 mm	Cabinet Door	25 U	Steel Door
26230-025	Light Grey	RAL 7035	1133 mm	Cabinet Door	25 U	Steel Door
25230-030	Black Grey	RAL 7021	736 mm	Cabinet Door	29 U	Steel Door
26230-030	Light Grey	RAL 7035	736 mm	Cabinet Door	29 U	Steel Door
25230-026	Black Grey	RAL 7021	1534 mm	Cabinet Door	34 U	Steel Door
26230-026	Light Grey	RAL 7035	1534 mm	Cabinet Door	34 U	Steel Door
25230-027	Black Grey	RAL 7021	1711 mm	Cabinet Door	38 U	Steel Door
26230-027	Light Grey	RAL 7035	1711 mm	Cabinet Door	38 U	Steel Door

CatalogNumber	Color	Color Code	Height	Product Type	Rack Height	Type
25230-028	Black Grey	RAL 7021	1933 mm	Cabinet Door	43 U	Steel Door
26230-028	Light Grey	RAL 7035	1933 mm	Cabinet Door	43 U	Steel Door
25230-029	Black Grey	RAL 7021	2111 mm	Cabinet Door	47 U	Steel Door
26230-029	Light Grey	RAL 7035	2111 mm	Cabinet Door	47 U	Steel Door

Table 2/2	
Catalog Number	Width
25230-020	553 mm
26230-020	553 mm
25230-021	553 mm
26230-021	553 mm
25230-022	553 mm
26230-022	553 mm
25230-023	553 mm
26230-023	553 mm
25230-024	553 mm
26230-024	553 mm
25230-025	553 mm
26230-025	553 mm
25230-030	553 mm

Catalog Number	Width
26230-030	553 mm
25230-026	553 mm
26230-026	553 mm
25230-027	553 mm
26230-027	553 mm
25230-028	553 mm
26230-028	553 mm
25230-029	553 mm
26230-029	553 mm

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE