

# Cable Entry Gland Plate Sealing Plug, CEAS

Sealing plugs for the CEP cable entry series.



## INDUSTRY STANDARDS

UL94 V-0 Flammability; File No. E61997

NEMA Type 1, 12, 4x (indoor only)

CE

IP66

## FEATURES

Finish: White

Pack quantity: 25 pcs

Description: The CEAS sealing plugs make it easy to close pierced, unused holes in CEP cable entries. The geometry of the head prevents the ingress of spray water or dust and ensures an IP66 protection rating

Temperature resistance: -40°C to +120°C

Flammability: UL94 V-0

Protection: IP66

Material: Polyamide 6.6

## SPECIFICATIONS

| Table 1/1      |                |        |       |       |                  |           |
|----------------|----------------|--------|-------|-------|------------------|-----------|
| Catalog Number | Article Number | Height | Width | Depth | Product Family   | Material  |
| CEAS02         | 58388          | 2mm    | 2mm   | 18mm  | Cable management | Polyamide |
| CEAS03         | 58389          | 3mm    | 3mm   | 18mm  | Cable management | Polyamide |
| CEAS04         | 58391          | 4mm    | 4mm   | 18mm  | Cable management | Polyamide |
| CEAS05         | 58392          | 5mm    | 5mm   | 18mm  | Cable management | Polyamide |
| CEAS06         | 58393          | 6mm    | 6mm   | 18mm  | Cable management | Polyamide |
| CEAS07         | 58394          | 7mm    | 7mm   | 18mm  | Cable management | Polyamide |
| CEAS09         | 58396          | 9mm    | 9mm   | 18mm  | Cable management | Polyamide |
| CEAS10         | 58397          | 10mm   | 10mm  | 18mm  | Cable management | Polyamide |
| CEAS11         | 58398          | 11mm   | 11mm  | 18mm  | Cable management | Polyamide |
| CEAS12         | 58399          | 12mm   | 12mm  | 18mm  | Cable management | Polyamide |
| CEAS13         | 58401          | 13mm   | 13mm  | 18mm  | Cable management | Polyamide |
| CEAS14         | 58402          | 14mm   | 14mm  | 18mm  | Cable management | Polyamide |
| CEAS15         | 58403          | 15mm   | 15mm  | 18mm  | Cable management | Polyamide |
| CEAS16         | 58404          | 16mm   | 16mm  | 18mm  | Cable management | Polyamide |
| CEAS17         | 58405          | 17mm   | 17mm  | 18mm  | Cable management | Polyamide |
| CEAS22         | 58406          | 22mm   | 22mm  | 18mm  | Cable management | Polyamide |
| CEAS08         | 58395          | 8mm    | 8mm   | 18mm  | Cable management | Polyamide |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper

installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**