

ProLine 100-mm Solid Base



ProLine 100-mm Solid Base is installed at the bottom of the enclosure. Side gland plates and drill points for locating optional casters are included.

FEATURES

EMC bases are finished with paint over plated surfaces

Side gland plates included

Casters not included, but drill points for installing them are

SPECIFICATIONS

Table 1/1						
Catalog Number	Article Number	Material	Finish	Color	Color Code	Thickness
PB1105	97770	Mild Steel	Powder Coated	Jet Black	RAL 9005	1.52mm
PB1105HF	12959	Mild Steel	Powder Coated	Jet Black	RAL 9005	1.52mm
PB1106	97780	Mild Steel	Powder Coated	Jet Black	RAL 9005	1.52mm
PB1106SS	32009	Stainless Steel 304	Brushed			1.52mm
PB1124	97800	Mild Steel	Powder Coated	Jet Black	RAL 9005	1.52mm
PB1125	97810	Mild Steel	Powder Coated	Jet Black	RAL 9005	1.52mm
PB1126	97820	Mild Steel	Powder Coated	Jet Black	RAL 9005	1.52mm
PB1126SS	32029	Stainless Steel 304	Brushed			1.52mm
PB1165	97840	Mild Steel	Powder Coated	Jet Black	RAL 9005	1.52mm
PB1166	97850	Mild Steel	Powder Coated	Jet Black	RAL 9005	1.52mm
PB145	25539	Mild Steel	Powder Coated	Jet Black	RAL 9005	1.52mm
PB146	25549	Mild Steel	Powder Coated	Jet Black	RAL 9005	1.52mm
PB164	97650	Mild Steel	Powder Coated	Jet Black	RAL 9005	1.52mm
PB165	97660	Mild Steel	Powder Coated	Jet Black	RAL 9005	1.52mm
PB165HF	12849	Mild Steel	Powder Coated	Jet Black	RAL 9005	1.52mm
PB166	97670	Mild Steel	Powder Coated	Jet Black	RAL 9005	1.52mm
PB166SS	31969	Stainless Steel 304	Brushed			1.52mm
PB176	97690	Mild Steel	Powder Coated	Jet Black	RAL 9005	1.52mm
PB184	97720	Mild Steel	Powder Coated	Jet Black	RAL 9005	1.52mm

Catalog Number	Article Number	Material	Finish	Color	Color Code	Thickness
PB184HF	12909	Mild Steel	Powder Coated	Jet Black	RAL 9005	1.52mm
PB185	97730	Mild Steel	Powder Coated	Jet Black	RAL 9005	1.52mm
PB185HF	12919	Mild Steel	Powder Coated	Jet Black	RAL 9005	1.52mm
PB186	97740	Mild Steel	Powder Coated	Jet Black	RAL 9005	1.52mm
PB1108	97790	Mild Steel	Powder Coated	Jet Black	RAL 9005	1.9mm
PB1108HF	12979	Mild Steel	Powder Coated	Jet Black	RAL 9005	1.9mm
PB1108SS	32019	Stainless Steel 304	Brushed			1.9mm
PB1128	97830	Mild Steel	Powder Coated	Jet Black	RAL 9005	1.9mm
PB1128SS	32039	Stainless Steel 304	Brushed			1.9mm
PB1168	97860	Mild Steel	Powder Coated	Jet Black	RAL 9005	1.9mm
PB168	97680	Mild Steel	Powder Coated	Jet Black	RAL 9005	1.9mm
PB168HF	12869	Mild Steel	Powder Coated	Jet Black	RAL 9005	1.9mm
PB168SS	31979	Stainless Steel 304	Brushed			1.9mm
PB178	97700	Mild Steel	Powder Coated	Jet Black	RAL 9005	1.9mm
PB179HF	12899	Mild Steel	Powder Coated	Jet Black	RAL 9005	1.9mm
PB188	97750	Mild Steel	Powder Coated	Jet Black	RAL 9005	1.9mm
PB189	97760	Mild Steel	Powder Coated	Jet Black	RAL 9005	1.9mm

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE