

ProLine G2 Partial Subpanel and Side-Mount Subpanel



The ProLine G2 Partial Subpanel secures to the frame or grid straps and facilitates component mounting without consumption of excess internal space; also available in side-mount configuration.

FEATURES

12 gauge (2.5mm) mild steel; available standard in painted white or conductive finish

Flanges on all four sides for increased rigidity

Partial subpanels can be placed in the rearmost position of the enclosure at any vertical height in 25-mm increments, or placed at any depth using grid straps (not included)

Side-mount partial subpanels can be placed on either side at any vertical height in 25-mm increments

All necessary mounting hardware is included

SPECIFICATIONS

Thickness: 2.66mm

Table 1/1

Catalog Number	Article Number	Material	Color	Finish	Quick Ship
P2PP1110	33545	Mild Steel	White	Powder Coated	No
P2PP1110G	33574	Mild Steel		Galvanized	No
P2PP1112	33546	Mild Steel	White	Powder Coated	No
P2PP1112G	33575	Mild Steel		Galvanized	No
P2PP114	33542	Mild Steel	White	Powder Coated	No
P2PP114G	33568	Mild Steel		Galvanized	No
P2PP116	33543	Mild Steel	White	Powder Coated	No
P2PP116G	33572	Mild Steel		Galvanized	No
P2PP118	33544	Mild Steel	White	Powder Coated	No
P2PP118G	33573	Mild Steel		Galvanized	No
P2PP510	33524	Mild Steel	White	Powder Coated	No
P2PP510G	33553	Mild Steel		Galvanized	No
P2PP512	33525	Mild Steel	White	Powder Coated	No
P2PP512G	33554	Mild Steel		Galvanized	No
P2PP54	33518	Mild Steel	White	Powder Coated	No
P2PP54G	33547	Mild Steel		Galvanized	No
P2PP56	33522	Mild Steel	White	Powder Coated	No
P2PP56G	33548	Mild Steel		Galvanized	No

Catalog Number	Article Number	Material	Color	Finish	Quick Ship
P2PP58	33523	Mild Steel	White	Powder Coated	No
P2PP58G	33552	Mild Steel		Galvanized	No
P2PP710	33532	Mild Steel	White	Powder Coated	No
P2PP710G	33558	Mild Steel		Galvanized	No
P2PP712	33533	Mild Steel	White	Powder Coated	No
P2PP712G	33562	Mild Steel		Galvanized	No
P2PP74	33526	Mild Steel	White	Powder Coated	No
P2PP74G	33555	Mild Steel		Galvanized	No
P2PP76	33527	Mild Steel	White	Powder Coated	No
P2PP76G	33556	Mild Steel		Galvanized	No
P2PP78	33528	Mild Steel	White	Powder Coated	No
P2PP78G	33557	Mild Steel		Galvanized	No
P2PP910	33537	Mild Steel	White	Powder Coated	No
P2PP910G	33566	Mild Steel		Galvanized	No
P2PP912	33538	Mild Steel	White	Powder Coated	No
P2PP912G	33567	Mild Steel		Galvanized	No
P2PP94	33534	Mild Steel	White	Powder Coated	No
P2PP94G	33563	Mild Steel		Galvanized	No
P2PP96	33535	Mild Steel	White	Powder Coated	No
P2PP96G	33564	Mild Steel		Galvanized	No

Catalog Number	Article Number	Material	Color	Finish	Quick Ship
P2PP98	33536	Mild Steel	White	Powder Coated	No
P2PP98G	33565	Mild Steel		Galvanized	No
P2PPSM1110	33601	Mild Steel	White	Powder Coated	No
P2PPSM1110G	33625	Mild Steel		Galvanized	No
P2PPSM114	33596	Mild Steel	White	Powder Coated	No
P2PPSM114G	33622	Mild Steel		Galvanized	No
P2PPSM115	33602	Mild Steel	White	Powder Coated	No
P2PPSM115G	33626	Mild Steel		Galvanized	No
P2PPSM116	33597	Mild Steel	White	Powder Coated	No
P2PPSM116G	33623	Mild Steel		Galvanized	No
P2PPSM118	33598	Mild Steel	White	Powder Coated	No
P2PPSM118G	33624	Mild Steel		Galvanized	No
P2PPSM510	33582	Mild Steel	White	Powder Coated	No
P2PPSM510G	33606	Mild Steel		Galvanized	No
P2PPSM54	33576	Mild Steel	White	Powder Coated	No
P2PPSM54G	33603	Mild Steel		Galvanized	No
P2PPSM55	33583	Mild Steel	White	Powder Coated	No
P2PPSM55G	33607	Mild Steel		Galvanized	No
P2PPSM56	33577	Mild Steel	White	Powder Coated	No
P2PPSM56G	33604	Mild Steel		Galvanized	No

Catalog Number	Article Number	Material	Color	Finish	Quick Ship
P2PPSM58	33578	Mild Steel	White	Powder Coated	No
P2PPSM58G	33605	Mild Steel		Galvanized	No
P2PPSM710	33587	Mild Steel	White	Powder Coated	No
P2PPSM710G	33613	Mild Steel		Galvanized	No
P2PPSM74	33584	Mild Steel	White	Powder Coated	No
P2PPSM74G	33608	Mild Steel		Galvanized	No
P2PPSM75	33588	Mild Steel	White	Powder Coated	No
P2PPSM75G	33614	Mild Steel		Galvanized	No
P2PPSM76	33585	Mild Steel	White	Powder Coated	No
P2PPSM76G	33611	Mild Steel		Galvanized	No
P2PPSM78	33586	Mild Steel	White	Powder Coated	No
P2PPSM78G	33612	Mild Steel		Galvanized	No
P2PPSM910	33594	Mild Steel	White	Powder Coated	No
P2PPSM910G	33618	Mild Steel		Galvanized	No
P2PPSM94	33591	Mild Steel	White	Powder Coated	No
P2PPSM94G	33615	Mild Steel		Galvanized	No
P2PPSM95	33595	Mild Steel	White	Powder Coated	No
P2PPSM95G	33621	Mild Steel		Galvanized	No
P2PPSM96	33592	Mild Steel	White	Powder Coated	No
P2PPSM96G	33616	Mild Steel		Galvanized	No

Catalog Number	Article Number	Material	Color	Finish	Quick Ship
P2PPSM98	33593	Mild Steel	White	Powder Coated	No
P2PPSM98G	33617	Mild Steel		Galvanized	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE