

White Coated Extreme Environments Enclosure



Extreme Environments Enclosure includes padlocking handle, lift off, lockable door. Available standard in White Painted 304SS with zinc plated internal components and EPDM replacement gasket. Gasket is removable, replaceable, and available for sale as a UL Listed field install kit. Gaskets are interchangeable among the Extreme Environments Enclosures of the same size.

This product utilizes the same back panel as A4SW3 for easy enclosure performance improvements for your next project with minimal to no design changes to layout.

INDUSTRY STANDARDS

304SS - UL 508A Recognized; Type 3R, 4, 4X File No. E61997. 316LSS - UL 508A Recognized; Type 12*, 13*, 3R, 4, 4X File No. E61997.

304SS - cUL Recognized per CSA C22.2 No 94; Type 3R, 4, 4X File No. E61997.

UL and cUL Classified to IEC 60529, IP66, IP69; File No. E503705

304SS - NEMA/EEMAC Type 3R, 4, 4X. 316LSS - NEMA/EEMAC Type 12, 13, 3R, 4, 4X.

IEC 60529 IP69 & 69K

Meets NEMA Type 3RX requirements

FEATURES

Seams continuously welded and ground smooth.

EPDM gasket - Temperature range: -50 to 120C (-58 to 248F).

Three-point latching on models 24-inches or taller.

Door easily removed by loosening set screws.

Data pocket is high-impact thermoplastic.

Collar studs provided for mounting optional panels.

Exterior Hardware made of corrosion resistant 316 stainless steel.

Bonding provision on door; grounding stud on body.

Painted enclosures use graffiti-resistant, cleanable, white paint.

SPECIFICATIONS

Table 1/1						
Catalog Number	Article Number	Height	Width	Depth	Material	Finish
XD242010E3PTS SW	56963	610mm	508mm	254mm	Stainless Steel 304	Powder Coated
XD242408E3PTS SW	56964	610mm	610mm	203mm	Stainless Steel 304	Powder Coated
XD242410E3PTS SW	56965	610mm	610mm	254mm	Stainless Steel 304	Powder Coated
XD242412E3PTS SW	56966	610mm	610mm	305mm	Stainless Steel 304	Powder Coated
XD302408E3PTS SW	56967	762mm	610mm	203mm	Stainless Steel 304	Powder Coated
XD302412E3PTS SW	56968	762mm	610mm	305mm	Stainless Steel 304	Powder Coated
XD303008E3PTS SW	56972	762mm	762mm	203mm	Stainless Steel 304	Powder Coated
XD303012E3PTS SW	56973	762mm	762mm	305mm	Stainless Steel 304	Powder Coated
XD363008E3PTS SW	56974	914mm	762mm	203mm	Stainless Steel 304	Powder Coated
XD363012E3PTS SW	56975	914mm	762mm	305mm	Stainless Steel 304	Powder Coated
XD363612E3PTS SW	56976	914mm	914mm	305mm	Stainless Steel 304	Powder Coated
XD423612E3PTS SW	56977	1067mm	914mm	305mm	Stainless Steel 304	Powder Coated
XD483612E3PTS SW	56978	1219mm	914mm	305mm	Stainless Steel 304	Powder Coated
XD483616E3PTS SW	56981	1219mm	914mm	406mm	Stainless Steel 304	Powder Coated

Catalog Number	Article Number	Height	Width	Depth	Material	Finish
XD603612E3PTS SW	56982	1524mm	914mm	305mm	Stainless Steel 304	Powder Coated

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE