


# EuropacPRO Cover Plate, Universal

## Power Utilities



A cover plate is used for electromagnetic shielding or as mechanical protection. The cover can be used is non-standard boards will be assembled into the subrack.

### CERTIFICATIONS



### FEATURES

Shielding is provided by optional EMC stainless steel gaskets, between cover plate and side panel

For variable positioning of horizontal rails e.g. for PCBs with non-standard formats

Perforation degree 58%

Suitable for use with all horizontal rails

### SPECIFICATIONS

Table 1/2

| Catalog Number | Rack Width | Depth  | Package Quantity | Product Family | Product Type | Type      |
|----------------|------------|--------|------------------|----------------|--------------|-----------|
| 24560-042      | 63 HP      | 235 mm | 1                | EuropacPRO     | Cover Plate  | Universal |
| 24560-054      | 84 HP      | 355 mm | 1                | EuropacPRO     | Cover Plate  | Universal |

| CatalogNumber | Rack Width | Depth  | Package Quantity | Product Family | Product Type | Type      |
|---------------|------------|--------|------------------|----------------|--------------|-----------|
| 24560-033     | 42 HP      | 295 mm | 1                | EuropacPRO     | Cover Plate  | Universal |
| 24560-043     | 63 HP      | 295 mm | 1                | EuropacPRO     | Cover Plate  | Universal |
| 24560-041     | 63 HP      | 175 mm | 1                | EuropacPRO     | Cover Plate  | Universal |
| 24560-032     | 42 HP      | 235 mm | 1                | EuropacPRO     | Cover Plate  | Universal |
| 24560-052     | 84 HP      | 235 mm | 1                | EuropacPRO     | Cover Plate  | Universal |
| 24560-055     | 84 HP      | 415 mm | 1                | EuropacPRO     | Cover Plate  | Universal |
| 24560-053     | 84 HP      | 295 mm | 1                | EuropacPRO     | Cover Plate  | Universal |
| 24560-031     | 42 HP      | 175 mm | 1                | EuropacPRO     | Cover Plate  | Universal |
| 24560-056     | 84 HP      | 475 mm | 1                | EuropacPRO     | Cover Plate  | Universal |
| 24560-051     | 84 HP      | 175 mm | 1                | EuropacPRO     | Cover Plate  | Universal |

Table 2/2

| Catalog Number | Works With | Package Unit |
|----------------|------------|--------------|
| 24560-042      | Sub racks  | Pair         |
| 24560-054      | Sub racks  | Pair         |
| 24560-033      | Sub racks  | Pair         |
| 24560-043      | Sub racks  | Pair         |
| 24560-041      | Sub racks  | Pair         |
| 24560-032      | Sub racks  | Pair         |
| 24560-052      | Sub racks  | Pair         |

| Catalog Number | Works With | Package Unit |
|----------------|------------|--------------|
| 24560-055      | Subracks   | Pair         |
| 24560-053      | Subracks   | Pair         |
| 24560-031      | Subracks   | Pair         |
| 24560-056      | Subracks   | Pair         |
| 24560-051      | Subracks   | Pair         |

## ADDITIONAL PRODUCT DETAILS

In addition, 4 contact strips per subrack are required to affix cover to horizontal rail.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**