

# Conductor Sleeve



## FEATURES

Used to adapt a limited range of smaller size cables to a larger size nVent ERICO Cadweld Mold

Provides strength and stability on finely-stranded copper conductors

## SPECIFICATIONS


**Material:** Copper

Table 1/1

Catalog Number	Article Number	Finish	Type	Length (L)	Thickness (T)	Diameter (Ø)
S429F2J16		Tinned	Flared	25.4mm	0.51 mm	12.19 mm
S429F2N16		Tinned	Flared	25.4mm	0.51 mm	13.72 mm
B112		Tinned	Straight	26.99mm	0.79 mm	5.38 mm
B1331K		Tinned	Straight	25.4mm	0.79 mm	3.56 mm
PBS24F		Tinned	Flared	38.1mm	0.79 mm	20.19 mm
S02F		Tinned	Flared	25.4mm	0.79 mm	15.52 mm

CatalogNumber	Article Number	Finish	Type	Length (L)	Thickness (T)	Diameter (Ø)
S03F		Tinned	Flared	25.4mm	0.79 mm	11.56 mm
S05F		Tinned	Flared	25.4mm	0.79 mm	9.93 mm
S07F		Tinned	Flared	25.4mm	0.79 mm	17.04 mm
S17F		Tinned	Flared	25.4mm	0.79 mm	8.74 mm
S429F3S20		Tinned	Flared	31.75mm	0.64 mm	23.62 mm
H101	180140		Straight	26mm	1 mm	6 mm
H102	180170		Straight	25mm	1.05 mm	4.3 mm
H102F	180390		Flared	26mm	1.05 mm	4.3 mm
H105	180230		Straight	23.5mm	1 mm	3 mm
H106AF	180260		Flared	35mm	1 mm	15 mm
H106F	180250		Flared	26mm	1 mm	15 mm
H113F	180360		Flared	26mm	1 mm	8 mm
H117	180430		Straight	25mm	1 mm	7 mm
H103	180180		Straight	25mm	1.2 mm	5.3 mm
180380	180380	Tinned	Flared	25mm	2.4 mm	5.3 mm

## DIAGRAMS



**WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

**Europe**

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

**Europe**

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

**APAC**

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**