

# Through Wall/Roof Connector



## CERTIFICATIONS



## FEATURES

- Can be used with air terminals or threaded rod
- Positive bolt tension cable clamping for conductors
- Includes washer and nut for secure connections

## SPECIFICATIONS

Table 1/1


Catalog Number	Material	Finish	Thread Size (TS)	Width (W)	Unit Weight	Depth (D)
LPA61058	Aluminum	Bare	5/8" UNC	46.74 mm	0.07 kg	36.07mm
LPA61012	Aluminum	Bare	1/2" UNC	46.74 mm	0.07 kg	36.07mm
LPC61038	Bronze	Bare	3/8" UNC	46.74 mm	0.17 kg	36.07mm

CatalogNumber	Material	Finish	Thread Size (TS)	Width (W)	Unit Weight	Depth (D)
LPC610BI58	Aluminum, Bronze, Stainless Steel 304 (EN 1.4301)	Bare	5/8" UNC	46.74 mm	0.17 kg	36.07mm
LPC61012	Bronze	Bare	1/2" UNC	46.74 mm	0.17 kg	36.07mm
LPC610BI38	Aluminum, Bronze, Stainless Steel 304 (EN 1.4301)	Bare	3/8" UNC	46.74 mm	0.17 kg	36.07mm
LPC61058	Bronze	Bare	5/8" UNC	46.74 mm	0.17 kg	36.07mm
LPC610BI12	Aluminum, Bronze, Stainless Steel 304 (EN 1.4301)	Bare	1/2" UNC	46.74 mm	0.17 kg	36.07mm
LPC610L12	Bronze	Tinned	1/2" UNC	46.74 mm	0.17 kg	36.07mm

## ADDITIONAL PRODUCT DETAILS

Stainless steel separator included with LPC610BI parts for bi-metallic applications.

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



WARNING: This product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov).

**North America**

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

**Europe**

Netherlands:

+31 800-0200135

France:

+33 800 901 793

**Europe**

Germany:

800 1890272

Other Countries:

+31 13 5835404

**APAC**

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**