

Fusion G7 Half-Height Side Panel



Fusion G7 half-height side panel furnished with mounting hardware.

FEATURES

Fusion G7 half-height side panel furnished with mounting hardware.

SPECIFICATIONS

Finish: Galvanized

Material: Mild Steel

Table 1/1

Catalog Number	Height	Width	Thickness	Fits Frame	Quick Ship
FUMP1025G030S	470mm	193mm	1.5mm	1000 x 250mm	No
FUMP1030G030S	470mm	241mm	1.5mm	1000 x 300mm	No
FUMP1040G030S	470mm	342mm	1.5mm	1000 x 400mm	No
FUMP1230G030S	569mm	241mm	1.5mm	1200 x 300mm	No
FUMP1232G030S	569mm	342mm	1.5mm	1200 x 400mm	No
FUMP1240G030S	569mm	266mm	1.5mm	1200 x 325mm	No
FUMP1532G030S	719mm	266mm	1.5mm	1500 x 325mm	No
FUMP1542G030S	719mm	365mm	1.5mm	1500 x 425mm	No
FUMP3015G030S	119mm	91mm	1.5mm	300 x 150mm	No
FUMP3020G030S	119mm	142mm	1.5mm	300 x 200mm	No
FUMP3022G030S	119mm	167mm	1.5mm	300 x 225mm	No
FUMP4015G030S	170mm	91mm	1.5mm	400 x 150mm	No
FUMP4022G030S	170mm	167mm	1.5mm	400 x 225mm	No
FUMP5022G030S	221mm	167mm	1.5mm	500 x 225mm	No
FUMP5030G030S	221mm	241mm	1.5mm	500 x 300mm	No
FUMP6020G030S	269mm	142mm	1.5mm	600 x 200mm	No
FUMP6022G030S	269mm	167mm	1.5mm	600 x 225mm	No

Catalog Number	Height	Width	Thickness	Fits Frame	Quick Ship
FUMP6030G030S	269mm	241mm	1.5mm	600 x 300mm	No
FUMP6032G030S	269mm	266mm	1.5mm	600 x 325mm	No
FUMP6040G030S	269mm	342mm	1.5mm	600 x 400mm	No
FUMP7025G030S	320mm	193mm	1.5mm	700 x 250mm	No
FUMP8022G030S	371mm	167mm	1.5mm	800 x 225mm	No
FUMP8030G030S	371mm	241mm	1.5mm	800 x 300mm	No
FUMP8032G030S	371mm	266mm	1.5mm	800 x 325mm	No
FUMP8042G030S	371mm	365mm	1.5mm	800 x 425mm	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE