

# ProLine G2 Solid Top

ProLine G2 Solid tops are used to close the top opening on an enclosure frame.



## FEATURES

---

Lifting eyes can be used to attach the solid top, in place of the included hardware

Seamless polyurethane gasket (UL component recognized) provides a water-tight, dust-tight seal against moisture and contaminants

Additional support provisions need to be made to support top mount air conditioners or other top mount accessories

Includes four M12 hex bolts for installation

Solid Tops are finished with paint over plated surfaces

## SPECIFICATIONS

**Thickness:** 1.52mm  
**Color:** Light Gray  
**Color Code:** RAL 7035

Table 1/1

| Catalog Number | Article Number | Height | Width | Depth | Material   | Finish                       |
|----------------|----------------|--------|-------|-------|------------|------------------------------|
| P2T104         | 32632          | 979mm  | 358mm | 16mm  | Mild Steel | Powder Coated                |
| P2T105         | 32633          | 979mm  | 459mm | 16mm  | Mild Steel | Powder Coated                |
| P2T106         | 32635          | 979mm  | 558mm | 16mm  | Mild Steel | Powder Coated                |
| P2T106HF       | 32634          | 979mm  | 558mm | 16mm  | Mild Steel | Galvanized,<br>Powder Coated |
| P2T108         | 32636          | 979mm  | 759mm | 16mm  | Mild Steel | Powder Coated                |
| P2T124         | 32637          | 1179mm | 358mm | 16mm  | Mild Steel | Powder Coated                |
| P2T125         | 32638          | 1179mm | 459mm | 16mm  | Mild Steel | Powder Coated                |
| P2T126         | 32642          | 1179mm | 558mm | 16mm  | Mild Steel | Powder Coated                |
| P2T128         | 32643          | 1179mm | 759mm | 16mm  | Mild Steel | Powder Coated                |
| P2T164         | 32644          | 1579mm | 358mm | 16mm  | Mild Steel | Powder Coated                |
| P2T165         | 32645          | 1579mm | 459mm | 16mm  | Mild Steel | Powder Coated                |
| P2T166         | 32646          | 1579mm | 558mm | 16mm  | Mild Steel | Powder Coated                |
| P2T168         | 32647          | 1579mm | 759mm | 16mm  | Mild Steel | Powder Coated                |
| P2T185         | 32648          | 1779mm | 459mm | 16mm  | Mild Steel | Powder Coated                |
| P2T186         | 32652          | 1779mm | 558mm | 16mm  | Mild Steel | Powder Coated                |
| P2T188         | 32653          | 1779mm | 759mm | 16mm  | Mild Steel | Powder Coated                |
| P2T45          | 32654          | 379mm  | 459mm | 16mm  | Mild Steel | Powder Coated                |

| Catalog Number | Article Number | Height | Width | Depth | Material   | Finish                       |
|----------------|----------------|--------|-------|-------|------------|------------------------------|
| P2T46          | 32655          | 379mm  | 558mm | 16mm  | Mild Steel | Powder Coated                |
| P2T64          | 32656          | 579mm  | 358mm | 16mm  | Mild Steel | Powder Coated                |
| P2T65          | 32657          | 579mm  | 459mm | 16mm  | Mild Steel | Powder Coated                |
| P2T66          | 32662          | 579mm  | 558mm | 16mm  | Mild Steel | Powder Coated                |
| P2T66HF        | 32658          | 579mm  | 558mm | 16mm  | Mild Steel | Galvanized,<br>Powder Coated |
| P2T68          | 32663          | 579mm  | 759mm | 16mm  | Mild Steel | Powder Coated                |
| P2T810         | 32664          | 779mm  | 960mm | 16mm  | Mild Steel | Powder Coated                |
| P2T84          | 32665          | 779mm  | 358mm | 16mm  | Mild Steel | Powder Coated                |
| P2T85          | 32666          | 779mm  | 459mm | 16mm  | Mild Steel | Powder Coated                |
| P2T86          | 32668          | 779mm  | 558mm | 16mm  | Mild Steel | Powder Coated                |
| P2T86HF        | 32667          | 779mm  | 558mm | 16mm  | Mild Steel | Galvanized,<br>Powder Coated |
| P2T88          | 32672          | 779mm  | 759mm | 16mm  | Mild Steel | Powder Coated                |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**